



| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | V2  | REVISED PER ECO-16-004223 | 19JUL2016 | NK  | MZ   |

D



C



B

A

- 1

BRASS PER ASTM B-36.
- 2

2.54um[.000100] MIN TIN-LEAD OVER 1.27um[.000050] MIN NICKEL.
- 3

SELECTIVELY PLATED 0.76um[.000030] MIN GOLD, FOR A DISTANCE OF 5.08[.200] FROM MATING END, GOLD FLASH ON REMAINDER, ALL OVER 1.27um[.000050] MIN NICKEL.
- 4

GOLD PLATING NOT TO APPEAR ON INSULATION SUPPORT STABILIZER.
- 5

POST WILL ACCEPT (SEE TABLE) TERMINATIONS.
- 6

.000100 MIN TIN OVER .000050 NICKEL. (POST).
- 7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

D



C

B

A

|          |             |             |            |                  |                  |                                   |
|----------|-------------|-------------|------------|------------------|------------------|-----------------------------------|
| OBSOLETE | 6           | 3           | SPECIAL    | 35.03<br>[1.379] | 14.86<br>[.585]  | <del>1-66471-9</del>              |
|          |             | 3           | 1          | 37.97<br>[1.495] | 17.81<br>[.701]  | 1-66471-8                         |
|          |             | 6           | 3          | 49.89<br>[1.964] | 29.74<br>[1.171] | 1-66471-7                         |
| OBSOLETE | 6           | 6           | 1          | 37.97<br>[1.495] | 17.81<br>[.701]  | <del>1-66471-6</del>              |
|          |             | 3           | 3          | 49.89<br>[1.964] | 29.74<br>[1.171] | 1-66471-5                         |
|          |             | 3           | SPECIAL    | 35.03<br>[1.379] | 14.86<br>[.585]  | <div>7</div> <del>1-66471-4</del> |
| OBSOLETE | 2           | 2           | SPECIAL    | 40.79<br>[1.606] | 20.65<br>[.813]  | <del>1-66471-0</del>              |
|          |             | 3           | 3          | 49.89<br>[1.964] | 29.74<br>[1.171] | 66471-9                           |
|          |             | 3           | 1          | 37.97<br>[1.495] | 17.81<br>[.701]  | 66471-7                           |
|          |             | 2           | 3          | 49.89<br>[1.964] | 29.74<br>[1.171] | 66471-3                           |
|          |             | 2           | 1          | 37.97<br>[1.495] | 17.81<br>[.701]  | 66471-1                           |
|          | POST FINISH | BODY FINISH | NO OF TERM | B                | A                | PART NUMBER                       |

66471

|   |  |   |   |  |           |            |               |     |    |
|---|--|---|---|--|-----------|------------|---------------|-----|----|
| THIS DRAWING IS A CONTROLLED DOCUMENT.  |  | DWN<br>C.REIFSNYDER<br>07 JUN 96          |  TE Connectivity |  |           |            |               |     |    |
|   |  | CHK<br>R.STONE<br>12 JUL 96               |   |  |           |            |               |     |    |
| DIMENSIONS:<br>mm [INCHES]  |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED: |   | NAME<br><br>PIN CONTACT, CRIMPED,<br>.062 DIA, .045 x .045 POST, |           |            |               |     |    |
|  |  | APVD<br>G.A.STEINHAUER<br>23 JUL 96       |   |  |           |            |               |     |    |
|   |  | PRODUCT SPEC<br>—                         |   |  |           |            |               |     |    |
|   |  | APPLICATION SPEC<br>—                     |   |  |           |            |               |     |    |
| MATERIAL  |  | FINISH                                    |   | SIZE   | CAGE CODE | DRAWING NO | RESTRICTED TO |     |    |
| SEE CALLOUTS  |  | SEE CALLOUTS                              |   | A2   | 00779     | C-66471    | —             |     |    |
| CUSTOMER DRAWING  |  |   |   | SCALE  | 4:1       | SHEET      | 1 of 1        | REV | V2 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[66471-3](#)