









RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE



2-2842269-0 AS SHOWN

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	06DEC2019	AY	PS
	A1	REMOVE POSITION 4	04JUN2020	AY	PS

- NOTES:
- MATERIAL
HOUSING : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
POST : COPPER ALLOY
FINISH : MIN. 2.0 μ m TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: TAPE AND REEL.
- $\triangle 3$ TOLERANCE NOT CUMULATIVE.

52.10	51.40	50	5-2842269-0
50.10	49.40	48	4-2842269-8
48.10	47.40	46	4-2842269-6
46.10	45.40	44	4-2842269-4
44.10	43.40	42	4-2842269-2
42.10	41.40	40	4-2842269-0
40.10	39.40	38	3-2842269-8
38.10	37.40	36	3-2842269-6
36.10	35.40	34	3-2842269-4
34.10	33.40	32	3-2842269-2
32.10	31.40	30	3-2842269-0
30.10	29.40	28	2-2842269-8
28.10	27.40	26	2-2842269-6
26.10	25.40	24	2-2842269-4
24.10	23.40	22	2-2842269-2
22.10	21.40	20	2-2842269-0
20.10	19.40	18	1-2842269-8
18.10	17.40	16	1-2842269-6
16.10	15.40	14	1-2842269-4
14.10	13.40	12	1-2842269-2
12.10	11.40	10	1-2842269-0
10.10	9.40	8	2842269-8
8.10	7.40	6	2842269-6
DIM "F"	DIM "E"	POS.	TE PN

CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 2° FINISH SEE NOTES
MATERIAL SEE NOTES	SEE NOTES
CUSTOMER DRAWING	
DWN ANKIL YADAV 29NOV2019 CHK KARTHIK JK 04DEC2019 APVD PRASHANTH S. 05DEC2019	
NAME AMPMODU 2mm SHROUDED HEADER, DUAL ROW, RIGHT ANGLE, Sn, TR	
SIZE A2	CAGE CODE 00779
DRAWING NO. 2842269	RESTRICTED TO -
SCALE 7:1	SHEET 1 OF 1
REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2842269-8](#)