




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-20-008004	11JUN2020	KR	DR



FOR 1.651(.064) TO 2.235(.088) WIRE INSULATION DIA.

329647	BAGGED KIT – LOOSE PIECE	1000
PART NUMBER	PACKAGE TYPE	QTY.

2	BUSHING	PTFE PER ASTM D3295, COLOR: NATURAL
1	WIRE SPLICE	COPPER (PER ASTM B152) GOLD PL. PER ASTM B488, TYPE II, 0.000127(.000050) MIN. EXT THK OVER NICKEL PL PER SAE AMS QQ-N-290 0.00762(.00030) MIN. EXT THK
1	SLEEVE ASSY	<u>INSULATION</u> : PTFE PER ASTM D3295, COLOR: NATURAL <u>RING</u> :ALUM(QQ-A-250/1) COLOR RED
QTY	DESCRIPTION	MATERIAL AND FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11JUN2020 RAGHAVENDRA K		 TE Connectivity			
		CHK 11JUN2020 DANIEL ROHDE					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME WIRE SPLICE KIT, BUTT, POST INSULATED, STRATO-THERM, WIRE SIZE: 18-16 AWG —			
		0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.127(.005) 4 PLC ± — ANGLES ± —					
MATERIAL SEE TABLE		FINISH SEE TABLE					
		APVD 11JUN2020 DANIEL ROHDE		SIZE A3			
		PRODUCT SPEC —		CAGE CODE 00779		DRAWING NO C-329647	
		APPLICATION SPEC —		RESTRICTED TO —		SCALE 1:1	
		WEIGHT —		SHEET 1 OF 1		REV C	
CUSTOMER DRAWING							

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[329647](#)