

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AN	ECO-20-004897	24AUG2020	SB	KJ

1. FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7532.
2. SWITCH SHOWN IN OPEN POSITION.
3. ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLUE.
4. LASER MARKING WILL VARY ON 2 AND 3 POSITION SIDES DUE TO SPACE RESTRICTIONS.

- 5

.315 DIMENSION APPLIES AT TERMINAL TIPS.
TERMINALS ARE .300-.000 AT MOUNTING SURFACE.
- 6

STRIPPABLE TRANSPARENT SEAL, SEE FIG 1.

<div>7</div> OBSOLETE	FIG 6	————	1.08	10	6-435640-1
		————	.58	5	6-435640-0
<div>7</div> OBSOLETE	FIG 7	————	.48	4	5-435640-9
		————	.88	8	5-435640-8
		————	.98	9	5-435640-7
<div>7</div> OBSOLETE	FIG 5	<div>6</div>	.68	6	5-435640-6
			.58	5	5-435640-5
			.48	4	5-435640-4
<div>7</div> OBSOLETE	FIG 2	<div>6</div>	.88	8	5-435640-3
	FIG 5	<div>6</div>	.88	8	5-435640-2
		————	1.08	10	5-435640-1
	FIG 3	<div>6</div>	.88	8	5-435640-0
		————	.88	8	4-435640-9
		————	.58	5	4-435640-8
<div>7</div> OBSOLETE	FIG 3	————	.88	8	4-435640-7
	NONE	————	1.28	12	4-435640-3
			1.08	10	4-435640-1
			.98	9	4-435640-0
			.88	8	3-435640-9
			.78	7	3-435640-8
			.68	6	3-435640-7
			.58	5	3-435640-6
			.48	4	3-435640-5
			.38	3	3-435640-4
			.28	2	3-435640-3
SUPSD BY 3-435668-3	FIG 4	————	1.28	12	3-435640-2
SUPSD BY 2-435668-6 3-1589670-4		————	.38	3	3-435640-0
	AS SHOWN	————	.28	2	2-435640-9
	FIG 4	————	.78	7	2-435640-2
<div>7</div> OBSOLETE	FIG 2	————	1.08	10	435640-7
		————	.98	9	435640-6
		————	.88	8	435640-5
		————	.68	6	435640-4
		————	.58	5	435640-3
		————	.48	4	435640-2
		————	.78	7	435640-1
	TOP MARKING	A	NO OF POSN		PART NO.

435640-4 SHOWN

SUPSD BY 3-435668-3
SUPSD BY 2-435668-6
3-1589670-4

SUPSD BY 5-5435640-4

SUPSD BY 4-5435640-8

CONTACT ARRANGEMENT

PROTECTIVE SEAL

MOUNTING SURFACE

.02+.01
STANDOFF, 4 PLC

.29±.02 TYP

FIG 1

CONTACT ARRANGEMENT




FIG 5




FIG 4




FIG 3




FIG 2




FIG 7







FIG 6



7

 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8 MARKS WILL BE ADDED BY LASER MARK PROCESS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.TALLEY 15NOV89	TE Connectivity	
DIMENSIONS: INCHES		CHK R.L.MILLER 06MAR90		
		APVD H.LEITER 06MAR90	NAME SWITCH ASSY, DIP, TYPE C, 7100 SERIES, SPST, STANDARD	
		PRODUCT SPEC	—	
MATERIAL HOUSING & ROCKERS: POLYESTER CONTACTS: COPPER ALLOY		APPLICATION SPEC	—	
FINISH CONTACTS: PLATED .000030 MIN GOLD IN CONTACT AREA OVER .000050 MIN NICKEL		WEIGHT —	SIZE A2	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 4:1	CAGE CODE 00779	REV AN
		SHEET 1 OF 1	DRAWING NO C-435640	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-435640](#)