

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECO-20-013368	22SEP20	RZ	HL

- 1

HOUSING MATERIAL: LIQUID CRYSTAL POLYMER
COLOR: NATURAL.
- 2



CONTACT MATERIAL: PHOSPHOR BRONZE
- 3

CONTACT FINISH:(B)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.0006 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- 4

PART MARKING LOCATED APPROXIMATELY AS SHOWN.
- 5

DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.
- 6

CONTACT FINISH:(B)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
0.00076 MIN NICKEL OR COBALT HARDENED GOLD
PER ASTM B-488 OVER UNDERPLATE.
ON LEADS:
0.0006 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.



RECOMMENDED CIRCUIT PATTERN
(COMPONENT SIDE)

OBSOLETE	10	5	11.88	30	3-5223016-1
OBSOLETE	260	130	131.88	330	1-5223016-1
OBSOLETE	118	59	119.88	300	1-5223016-0
OBSOLETE	106	53	107.88	270	5223016-9
	94	47	95.88	240	5223016-8
OBSOLETE	82	41	83.88	210	5223016-7
OBSOLETE	140	70	71.88	180	5223016-6
OBSOLETE	58	29	59.88	150	5223016-5
	46	23	47.88	120	5223016-4
	34	17	35.88	90	5223016-3
	22	11	23.88	60	5223016-2
	10	5	11.88	30	5223016-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.MCMMASTER 22NOV04	TE Connectivity		
DIMENSIONS: mm		CHK R.WERTZ 22NOV04	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.WERTZ 22NOV04	PRODUCT SPEC		
0 PLC $\pm$ -		APPLICATION SPEC		SIZE	
1 PLC $\pm$ 0.13		—		CAGE CODE	
2 PLC $\pm$ 0.13		—		DRAWING NO	
3 PLC $\pm$ -		—		RESTRICTED TO	
4 PLC $\pm$ -		—		—	
ANGLES $\pm$ -		—		—	
FINISH		WEIGHT		—	
—		0.000000		—	
—		A1 00779		—	
—		C=5223016		—	
—		CUSTOMER DRAWING		—	
—		SCALE		—	
—		4:1		—	
—		SHEET		—	
—		1 of 1		—	
—		REV		—	
—		—		—	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5223016-5](#)