





- ⚠ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER.
COLOR: NATURAL.
- ⚠ CONTACT MATERIAL: PHOSPHOR BRONZE.
- ⚠ CONTACT FINISH:(B)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.0006 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- ⚠ PART MARKING, LOCATED APPROXIMATELY AS SHOWN.
- 5. SEE SHEET 2 FOR SEQUENCING CHARTS.
- ⚠ DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.
- ⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DNN 15DEC04	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	± -	CHK R.WERTZ	15DEC04
1 PLC	± -	APVO R.WERTZ	15DEC04
2 PLC	± 0.13	PRODUCT SPEC	
3 PLC	± -	APPLICATION SPEC	
4 PLC	± -		
5 PLC	± -		
6 PLC	± -		
7 PLC	± -		
8 PLC	± -		
9 PLC	± -		
MATERIAL	FINISH	SIZE	CAGE CODE DRAWING NO.
1	2	0	A1 00779 C-5223611
3			CUSTOMER DRAWING
RESTRICED TO		SCALE 4:1 SHEET 1 OF 2 REV D	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DNW	APVD
	-	SEE SHEET 1	-	-	-

D	-	E	E	-	E	E	E	E	E	D			
C	E	E	E	E	E	E	E	E	E	C			
B	E	E	E	E	E	E	E	E	E	B			
A	-	-	-	-	N	N	N	T	T	A			
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

5223611-1
OBSOLETE

PART NUMBER

D	E	E	E	E	E	E	E	E	E	D			
C	E	E	E	E	E	E	E	E	E	C			
B	E	E	E	E	E	E	E	E	E	B			
A	E	E	E	E	E	E	E	E	E	A			
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

2-5223611-8
7

PART NUMBER

D	E	E	E	E	E	E	E	E	E	D			
C	E	E	E	E	E	E	E	E	E	C			
B	E	E	E	E	E	E	E	E	E	B			
A	E	E	E	E	E	E	E	E	E	A			
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

2-5223611-9
7

PART NUMBER

D	T	A	A	A	A	T	A	T	A	T	D		
C	J	A	A	A	A	T	T	A	T	A	C		
B	J	A	A	A	A	T	A	T	A	T	B		
A	J	A	A	A	A	T	T	A	T	A	A		
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

PART NUMBER

D	A	A	A	A	A	A	A	A	A	A	D		
C	A	A	A	A	A	A	A	A	A	A	C		
B	J	J	J	J	J	J	J	J	J	J	B		
A	A	A	A	A	A	A	A	A	A	A	A		
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

PART NUMBER

D	T	J	J	J	J	J	J	J	J	T	D		
C	T	J	J	J	J	J	J	J	J	J	C		
B	T	J	J	J	J	J	J	J	J	J	B		
A	T	J	J	J	J	J	J	J	J	J	A		
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

PART NUMBER

D	SS	X	X	X	X	X	X	SS	D				
C	SS	X	X	X	X	X	X	SS	C				
B	SS	X	X	X	X	X	X	SS	B				
A	SS	X	X	X	X	X	X	SS	A				
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

PART NUMBER

D	X	X	X	X	X	X	X	X	X	X	D		
C	X	X	X	X	X	X	X	X	X	X	C		
B	X	X	X	X	X	X	X	X	X	X	B		
A	X	X	X	X	X	X	X	X	X	X	A		
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

PART NUMBER

D	E	E	E	E	E	E	E	E	E	T	D		
C	E	E	E	E	E	E	E	E	E	E	C		
B	N	E	E	E	E	E	E	N	B				
A	E	E	E	E	E	E	E	E	E	T	A		
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

PART NUMBER

D	T	J	J	J	J	T	D						
C	T	J	J	J	J	T	C						
B	T	J	J	J	J	T	B						
A	T	J	J	J	J	T	A						
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

PART NUMBER

D	E	E	E	E	E	E	E	D					
C	E	E	E	E	E	E	E	C					
B	E	E	E	E	E	E	E	B					
A	N	N	N	T	N	N	N	A					
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-5223611-4](#)