

4

3

2

1

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	R4	PART STATUS UPATED IN PART LIST TABLE	16FEB2018	SD	PS



NOTES

- 1 WILL ALSO MATE W/OTHER CONNECTORS WHICH ARE COMPATIBLE WITH THE $.006$ END DIM.
- 2 OBSOLETE PART NUMBER.
- 3 $.000100$ – $.000200$ BRIGHT TIN–LEAD OVER $.000050$ NICKEL
- 4 $.000100$ – $.000200$ BRIGHT TIN OVER $.000050$ – $.000100$ NICKEL
- 5 PRELIMINARY PART.
- 6 $.000100$ – $.000200$ MATTE TIN OVER $.000050$ – $.000100$ NICKEL
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN — 12 SEP 75		 TE Connectivity	
		CHK — 12 SEP 75			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD — 15 SEP 75	
		0 PLC ± —		NAME HEADER ASSEMBLY MOD II, .100 C/L .025 SQUARE POST, WITH DETENT —	
		1 PLC ± —			
		2 PLC ± —			
		3 PLC ± .005			
4 PLC ± —		PRODUCT SPEC —			
ANGLES ± —		APPLICATION SPEC —			
MATERIAL		FINISH		WEIGHT —	
HSG: GLASS FILLED NYLON COLOR: BLACK CONTACT: PHOS BRONZE		SEE TABLE		A2 00779 C-87589	
CUSTOMER DRAWING				SCALE 3:1	
				SHEET 1 OF 2	
				REV R4	

87589

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-87589-6](#)