

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- - -

© COPYRIGHT - TE Connectivity Ltd.

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWN	09AUG2019	RV	DH


Ordering Information (All "X's" must be included to complete part number)

SCE	R	X	2	2	A	C	A
Series SCE True Off-delay Timer	Output Rating W = 10A (SPDT) X = 5A (DPDT)	Output 1 = SPDT (W) 2 = DPDT (W)	Timing Range A = 0.1 to 3 sec. B = 0.5 to 15 sec. C = 1 to 30 sec. E = 4 to 120 sec. G = 10 to 300 sec. L = 0.33 to 10 min.	Operating Mode 2 = True Off-Delay	Operating Voltage (+10%, -15%) A = 120VAC, 50/60 Hz. / 125VDC E = 24VAC, 50/60 Hz. / 24VDC F = 48VAC, 50/60 Hz. / 48VDC	Timing Adjustment A = Knob Adjust F = Fixed Times -Specify time delay in seconds per the following examples: XF9.000 = 9 sec. XF99.00 = 99 sec. XF999.0 = 9999 sec. XF1000 = 1000 sec.	Agency Recognition R = UL recognized


Wiring Diagrams (Bottom Views)



Fixed Time Or Knob Adjust




Fixed Time Or Knob Adjust



Outline Dimensions

ALL DIMENSIONS ARE IN INCHES[MM].

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RV	09AUG2019		 TE Connectivity					
		CHK RV	09AUG2019							
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD DH	09AUG2019		NAME SCE SERIES TIME DELAY RELAY - -					
		PRODUCT SPEC -								
		APPLICATION SPEC -		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
		WEIGHT -		A3	-	C-SCE-SERIES	-			
MATERIAL -		CUSTOMER DRAWING			SCALE	NTS	SHEET	1 OF 1	REV	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1472958-2](#)