



8		7	
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
(C) COPYRIGHT By -		ALL RIGHTS RESERVED.	
DESCRIPTION	MATERIAL	FINISH	
MODULE ASSEMBLY	EPOXY THERMOSET	COLOR: BLACK	
GROMMET	FLOURSILICONE 40/50 PER MIL-R-25988	COLOR: NATURAL	
CONTACT SOCKET	BERYLLIUM COPPER PER ASTM-B194	GOLD PLATE PER MIL-G-45204	
RETAINING CLIP	BERYLLIUM COPPER PER ASTM-B194 OR STAINLESS STEEL PER QQ-S-766	NONE	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G		REVISED PER ECO 20-001680	2-7-20	CT	VR



(02) (03) (04)




(06) (07) (08)




(11) (12) (16)

BUSSING ARRANGEMENTS



- 1 MODULE ASSEMBLY MARKED WITH "TE", TE PART NO. AND DATE CODE .060 MINIMUM HIGH CHARACTERS ON EITHER SIDE.
- 2 MARK MODULE ASSEMBLY WITH CUSTOMER PART NO. ON EITHER SIDE.
- 3 BUSSING ARRANGEMENT OUTLINE DENOTES INTERNAL ARRANGEMENT OF CONTACT SOCKETS.
4. ROLLS ROYCE QUALITY SPECIFICATION CQC-103 IS INVOLVED FOR THIS PART NO.
- 5 MODULE IS MARKED WITH WORD "TOP" IN LOCATION SHOWN.

MRFB16E16-204									X	592814-9
MRFB16E12-204								X		592814-8
MRFB16E11-204							X			592814-7
MRFB16E08-204						X				592814-6
MRFB16E07-204					X					592814-5
MRFB16E06-204				X						592814-4
MRFB16E04-204			X							592814-3
MRFB16E03-204		X								592814-2
MRFB16E02-204	X									592814-1
CUSTOMER PART NO. 	02	03	04	06	07	08	11	12	16	PART NO.
	BUSSING ARRANGEMENTS									

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N. FRITZ 09-22-93	TE Connectivity	
		CHK R. RYAN 09-23-93		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	MODULE, FEED-THROUGH ASSEMBLY, SIZE 16 TJ	
MATERIAL		FINISH	—	
		WEIGHT	0.000000	
		CUSTOMER DRAWING	A1 00779 592814	
		SCALE	2:1	
		SHEET	1 OF 1	
		REV	G	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[592814-1](#)