




THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LYR	DESCRIPTION	DATE	OWN
CM	00	P		REVISED PER ECR-20-000541	15MAY2020	PC

YES	71.12	[2.800]	28	5-640440-8
YES	68.58	[2.700]	27	5-640440-7
YES	66.04	[2.600]	26	5-640440-6
YES	63.50	[2.500]	25	5-640440-5
YES	60.96	[2.400]	24	5-640440-4
YES	58.42	[2.300]	23	5-640440-3
YES	55.88	[2.200]	22	5-640440-2
YES	53.34	[2.100]	21	5-640440-1
YES	50.80	[2.000]	20	5-640440-0
YES	48.26	[1.900]	19	4-640440-9
YES	45.72	[1.800]	18	4-640440-8
YES	43.18	[1.700]	17	4-640440-7
YES	40.64	[1.600]	16	4-640440-6
YES	38.10	[1.500]	15	4-640440-5
YES	35.56	[1.400]	14	4-640440-4
YES	33.02	[1.300]	13	4-640440-3
YES	30.48	[1.200]	12	4-640440-2
YES	27.94	[1.100]	11	4-640440-1
YES	25.40	[1.000]	10	4-640440-0
YES	22.86	[.900]	9	3-640440-9
YES	20.32	[.800]	8	3-640440-8
YES	17.78	[.700]	7	3-640440-7
YES	15.24	[.600]	6	3-640440-6
YES	12.70	[.500]	5	3-640440-5
YES	10.16	[.400]	4	3-640440-4
YES	7.62	[.300]	3	3-640440-3
YES	5.08	[.200]	2	3-640440-2
NO	71.12	[2.800]	28	2-640440-8 SUP BY 5-640440-8
NO	68.58	[2.700]	27	2-640440-7 SUP BY 5-640440-7
NO	66.04	[2.600]	26	2-640440-6 SUP BY 5-640440-6
NO	63.50	[2.500]	25	2-640440-5 SUP BY 5-640440-5
NO	60.96	[2.400]	24	2-640440-4 SUP BY 5-640440-4
NO	58.42	[2.300]	23	2-640440-3 SUP BY 5-640440-3
NO	55.88	[2.200]	22	2-640440-2 SUP BY 5-640440-2
NO	53.34	[2.100]	21	2-640440-1 SUP BY 5-640440-1
NO	50.80	[2.000]	20	2-640440-0 SUP BY 5-640440-0
NO	48.26	[1.900]	19	1-640440-9 SUP BY 4-640440-9
NO	45.72	[1.800]	18	1-640440-8 SUP BY 4-640440-8
NO	43.18	[1.700]	17	1-640440-7 SUP BY 4-640440-7
NO	40.64	[1.600]	16	1-640440-6 SUP BY 4-640440-6
NO	38.10	[1.500]	15	1-640440-5 SUP BY 4-640440-5
NO	35.56	[1.400]	14	1-640440-4 SUP BY 4-640440-4
NO	33.02	[1.300]	13	1-640440-3 SUP BY 4-640440-3
NO	30.48	[1.200]	12	1-640440-2 SUP BY 4-640440-2
NO	27.94	[1.100]	11	1-640440-1 SUP BY 4-640440-1
NO	25.40	[1.000]	10	1-640440-0 SUP BY 4-640440-0
NO	22.86	[.900]	9	640440-9 SUP BY 3-640440-9
NO	20.32	[.800]	8	640440-8 SUP BY 3-640440-8
NO	17.78	[.700]	7	640440-7 SUP BY 3-640440-7
NO	15.24	[.600]	6	640440-6 SUP BY 3-640440-6
NO	12.70	[.500]	5	640440-5 SUP BY 3-640440-5
NO	10.16	[.400]	4	640440-4 SUP BY 3-640440-4
NO	7.62	[.300]	3	640440-3 SUP BY 3-640440-3
NO	5.08	[.200]	2	640440-2 SUP BY 3-640440-2

7



- 1 MATERIAL: CONNECTOR - NYLON UL94V-2 (RED).
CONTACTS - 0.30[.012] THICK COPPER ALLOY
BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
FOR 640440-2 THRU 2-640440-8.
MATTE WHISKER MITIGATED TIN .00203[.000080] MIN THICKNESS OVER
NICKEL UNDERPLATE FOR 3-640440-2 THRU 5-640440-8.
- 2 CONTACTS ACCEPT 22 AWG WIRE WITH 1.52[.060] MAX
INSULATION DIAMETER.
- 3 CONTACTS MUST ACCEPT 0.64±0.03[.025±.001]
POST AND REMAIN LOCKED IN POSITION.
- 4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY
NOT APPEAR ON ALL ASSEMBLIES.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP.
- 7 OBSOLETE PARTS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWR S. CARPENTER 09/JUN/2003	 TE Connectivity	
		CHK D. BOSSI 09/JUN/2003		
DIMENSIONS: INCHES		APVD D. BOSSI 09/JUN/2003	NAME	
		PRODUCT SPEC		
		108-1050		
		APPLICATION SPEC		
		114-1019		
MATERIAL		WEIGHT		
FINISH		RESTRICTED TO		
		—		
		CUSTOMER DRAWING		
		SIZE		SCALE
		A2		5:1
		CAGE CODE		SHEET
		00779		1 of 1
		DRAWING NO		REV
		C640440		P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[640440-8](#)