

















LOCALIZED AREA	OBSOLETE	STANDARD			STRIP	7-66505-0
		SMALL PACK			LOOSE PIECE	6-66505-9
SUPERSEDED BY 66505-9		STANDARD			LOOSE PIECE	6-66505-2
	OBSOLETE	STANDARD			STRIP	6-66505-0
	OBSOLETE	STANDARD			LOOSE PIECE	5-66505-9
	OBSOLETE	STANDARD			STRIP	5-66505-7
	 OBSOLETE	STANDARD			STRIP	5-66505-5
		STANDARD			STRIP	2-66505-7
SUPERSEDED BY 5-66505-7		STANDARD			STRIP	1-66505-4
		STANDARD			STRIP	1-66505-3
	OBSOLETE	STANDARD			STRIP	1-66505-2
		STANDARD			LOOSE PIECE	1-66505-0
		STANDARD			LOOSE PIECE	66505-9
		STANDARD			LOOSE PIECE	66505-8
		STANDARD			STRIP	66505-4
		STANDARD			STRIP	66505-3
		STANDARD			STRIP	66505-2
		PACKAGING TYPE	FINISH	USE	TYPE	PART NUMBER



SECTION Y—Y
SCALE 20:1

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN C. RICHARD 1-6-87		 TE Connectivity				
		CHK S. WELDON 1-7-87						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SOCKET CONTACT, SIZE 20 DF, 24-28 AWG, W/ .030-.040 DIA INSULATION SUPPORT,				
		APVD —						
		PRODUCT SPEC —						
		APPLICATION SPEC 114-10000						
MATERIAL PHOSPHOR BRONZE		FINISH  SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C=66505	RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 10:1	SHEET 1 of 1	REV AT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[66505-2](#)