

| LOC | DIST | REVISIONS |     |                           |           |     |      |
|-----|------|-----------|-----|---------------------------|-----------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
| GP  | 00   |           | K   | REVISED PER ECO-11-006478 | 30MAR2011 | CJV | CWR  |

D

C

B


A

D

C


B

A



SECTION B-B

- 1 GOLD PLATING PER MIL-G-45204, TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- 2 0.76μm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA, 2.54μm [.000100] MIN BRIGHT TIN OR BRIGHT TIN-LEAD IN MIN LOCALIZED TIN PLATE AREA, ALL OVER 0.76μm [.000030] MIN NICKEL.
- 3 GOLD FLASH IN LOCALIZED GOLD PLATE AREA, 2.54μm [.000100] MIN BRIGHT TIN OR BRIGHT TIN-LEAD IN MIN LOCALIZED TIN PLATE AREA, ALL OVER 0.76μm [.000030] MIN NICKEL.
4. MAX INSULATION OD = .060.
- 5 0.76μm [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA, 2.54μm [.000100] MIN MATTE TIN IN MIN LOCALIZED TIN PLATE AREA, ALL OVER 0.76μm [.000030] MIN NICKEL.



|          |   |             |
|----------|---|-------------|
| OBSOLETE | 5 | 745931-8    |
|          | 3 | 745931-5    |
|          | 2 | 745931-3    |
| FINISH   |   | PART NUMBER |

|                                             |  |                               |                                                                         |                    |                        |                    |
|---------------------------------------------|--|-------------------------------|-------------------------------------------------------------------------|--------------------|------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.      |  | DWN<br>C. RICHARD<br>03/19/90 | TE Connectivity                                                         |                    |                        |                    |
| DIMENSIONS:<br>INCHES                       |  | CHK<br>W. LENKER<br>3-22-90   |                                                                         |                    |                        |                    |
|                                             |  | APVD<br>-                     | NAME<br>CONTACT SOCKET, MASS<br>TERMINATION, #26-30, HDE-20,<br>AMPLITE |                    |                        |                    |
|                                             |  | PRODUCT SPEC<br>-             |                                                                         |                    |                        |                    |
|                                             |  | APPLICATION SPEC<br>-         |                                                                         |                    |                        |                    |
| MATERIAL<br>PHOSPHOR BRONZE PER<br>QQ-B-750 |  | WEIGHT<br>-                   | SIZE<br>A2                                                              | CAGE CODE<br>00779 | DRAWING NO<br>C=745931 | RESTRICTED TO<br>- |
| FINISH<br>1                                 |  | CUSTOMER DRAWING              | SCALE<br>10:1                                                           | SHEET<br>1 of 1    | REV<br>K               |                    |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[745931-8](#)