


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AC 1	TOLERANCE ADDED FOR DIMENSION 0.63	17JUN2019	SS	PS

"F" = GOLD AREA




DIMENSION					PART- NO.			PART- NO.			PART- NO.		
					SELECTIVE GOLD PLATED			TIN PLATED			SELECTIVE GOLD PLATED		
A	B	C	F	-	1	5	7	WEIGHT POS. PER ROW			3	4	7
12.7	6.7	3.2	4.4	-	826629			826926					
12.0	6.7	2.5	4.4	-	826630			826935					
11.8	5.8	3.2	4.4	-	826646			826936			829070		
11.1	5.8	2.5	4.4	-	826647			826937					
14.0	8.0	3.2	4.4	-	826648			826938					
13.3	8.0	2.5	4.4	-	826649			826939					
12.7	6.7	3.2	5.5	-	-			-			828356		

CONTACT PIN	CuZn	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

- 1 MATING SIDE : AREA "F" MIN 0.7µm PdNi + MIN 0.1µm GOLD OVER 1.27µm NICKEL BY AREA "B" SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 2 MATING AND SOLDER SIDE : MIN 3µm TIN OVER 1.27µm NICKEL
- 3 MATING SIDE: AREA "F" 0.13µm GOLD OVER 1.27µm NICKEL BY AREA "B" SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 4 COLOR OF HOUSING: GREY
- 5 COLOR OF HOUSING: GREEN
- 6 TOLERANCES NOT CUMULATIVE
- 7 THE NUMBER OF POSITION PER ROW HAS TO BE ADDED TO THE BASE NO. AS A DASH NO. EG: 2-826629-0 = 20 POSITIONS
- THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR FOR THE WEIGHT DETERMINATION E.G: 20 X 0.0654 g = 1.308 g
- 8 OBSOLETE



SCALE 8:1
LAYOUT FOR HOLES ON PCB

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN G.HOLAUS 10NOV1989	TE Connectivity		
			CHK SCHAAERSCHMIDT M.			
DIMENSIONS: mm			APVD	NAME AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT		
			TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm 6			
			0 PLC ±	SIZE 114-25011		
			1 PLC ±			
			2 PLC ±	CAGE CODE 00779		
			3 PLC ±			
			4 PLC ±	DRAWING NO 826629		
			ANGLES ±			
MATERIAL SEE TABLE			FINISH	RESTRICTED TO		
				SCALE 5:1 SHEET 1 OF 4 REV AC 1		

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2019

© COPYRIGHT 2019

BY- TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

POS. X 2.54 = L±0.5

(L-2.54)±0.1

2.54 ±0.1

2.8

2.54 ±0.1

5.0

F

B

A

0.3

C REF

0.63 ±0.05

"F" = GOLD AREA

(L-2.54)±0.1

2.54 ±0.1

2.54 ±0.1

1 ±0.05

SCALE 8:1

LAYOUT FOR HOLES ON PCB

DIMENSION					PART-NO.		PART- NO.			PART- NO.			
A	B	C	F	-	SELECTIVE GOLD PLATED			TIN PLATED	WEIGHT POS. PER ROW	SELECTIVE GOLD PLATED			WEIGHT POS. PER ROW
					1	5	7	2		5	7	3	
12.7	6.7	3.2	5.5	-	826632			826925	0.1276 g	828420			0.1272 g
12.0	6.7	2.5	4.4	-	826633			826941	0.1226 g				
11.8	5.8	3.2	4.4	-	826656			826942	0.1212 g	828533			0.1209 g
11.1	5.8	2.5	4.4	-	826657			826943	0.1162 g				
14.0	8.0	3.2	4.4	-	826658			826944	0.1366 g				
13.3	8.0	2.5	4.4	-	826659			826945	0.1316 g				

CONTACT PIN	CuZn	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

1MATING SIDE : AREA "F" MIN 0.7µm PdNi + MIN 0.1µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL

2MATING AND SOLDER SIDE : MIN 3µm TIN OVER 1.27µm NICKEL

3MATING SIDE: AREA "F" 0.13µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL

4COLOR OF HOUSING: GREY

5COLOR OF HOUSING: GREEN

6TOLERANCES NOT CUMULATIVE

7THE NUMBER OF POSITION PER ROW HAS TO BE ADDED TO THE BASE NO. AS A DASH NO.
EG: 2-826632-0 = 20 POSITIONS

THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR FOR THE WEIGHT DETERMINATION
E.G: 20 X 0.1276 g = 2.552 g

8OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN G.HOLAUS 10NOV1989
CHK SCHAAERSCHMIDT M.
APVD

DIMENSIONS: mm

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm

6

MATERIAL SEE TABLE

-

PRODUCT SPEC 108-18012

APPLICATION SPEC 114-25011

WEIGHT -

CUSTOMER DRAWING

NAME AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT

SIZE A2

CAGE CODE 00779

DRAWING NO C-826629

RESTRICTED TO -

SCALE 5:1

SHEET 2 OF 4

REV AC1

1471-9 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

D



"F" = GOLD AREA


DIMENSION					PART-NO.		PART- NO.		PART- NO.	
					SELECTIVE GOLD PLATED		TIN PLATED	WEIGHT POS. PER ROW	SELECTIVE GOLD PLATED	
B	C	D	F	-	1	5	7		3	4
6.7	3.2	1.3	4.4	-	826631	0.0757 g	826947	0.0760 g		
6.7	2.5	1.3	4.4	-	826651	0.0731 g	826948	0.0735 g		
5.8	3.2	1.3	4.4	-	826652	0.0726 g	826949	0.0728 g	829071	0.0726 g
5.8	2.5	1.3	4.4	-	826653	0.0701 g	826950	0.0704 g		
8.0	3.2	1.3	4.4	-	826654	0.0803 g	826951	0.0807 g		
8.0	2.5	1.3	4.4	-	826655	0.0777 g	826952	0.0782 g		
6.7	3.2	1.3	5.5	-	-	-	-	-	828419	0.0758 g

CONTACT PIN	CuZn	SEE TABLE
CONTACT PIN	CuSn6	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

- 1 MATING SIDE : AREA "F" MIN 0.7µm PdNi + MIN 0.1µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 2 MATING AND SOLDER SIDE : MIN 3µm TIN OVER 1.27µm NICKEL
- 3 MATING SIDE: AREA "F" 0.13µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 4 COLOR OF HOUSING: GREY
- 5 COLOR OF HOUSING: GREEN
- 6 TOLERANCES NOT CUMULATIVE
- 7 THE NUMBER OF POSITION PER ROW HAS TO BE ADDED TO THE BASE NO. AS A DASH NO.
EG: 2-826631-0 = 20 POSITIONS
- THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR FOR THE WEIGHT DETERMINATION
E.G: 20 X 0.0757 g = 1.514 g
- 8 OBSOLETE
- 10 MATING AND SOLDER SIDE : 2µm TIN OVER 1.27µm NICKEL

B



SCALE 8:1
LAYOUT FOR HOLES ON PCB

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G.HOLAUS CHK SCHAAERSCHMIDT M. APVD -	10NOV1989	TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm	6		NAME AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT	
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC 108-18012 APPLICATION SPEC 114-25011 WEIGHT -	SIZE A2	CAGE CODE 00779
MATERIAL SEE TABLE			CUSTOMER DRAWING	DRAWING NO C-826629	RESTRICTED TO -
				SCALE 5:1	SHEET 3 OF 4
					REV AC 1

D



"F" = GOLD AREA

DIMENSION					PART-NO.		PART- NO.		PART- NO.	
					SELECTIVE GOLD PLATED		TIN PLATED		SELECTIVE GOLD PLATED	
B	C	D	F	-		WEIGHT POS. PER ROW		WEIGHT POS. PER ROW		WEIGHT POS. PER ROW
6.7	3.2	1.3	4.4	-	826634	0.1646 g	826953	0.1656 g	828418	0.1651 g
6.7	2.5	1.3	4.4	-	826661	0.1597 g	826954	0.1606 g		
5.8	3.2	1.3	4.4	-	826662	0.1587 g	826955	0.1603 g	829072	0.1587 g
5.8	2.5	1.3	4.4	-	826663	0.1538 g	826956	0.1542 g		
8.0	3.2	1.3	4.4	-	826664	0.1741 g	826957	0.1749 g		
8.0	2.5	1.3	4.4	-	826665	0.1687 g	826958	0.1699 g		

CONTACT PIN	CuZn	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

MATING SIDE : AREA "F" MIN 0.7µm PdNi + MIN 0.1µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL

MATING AND SOLDER SIDE : MIN 3µm TIN OVER 1.27µm NICKEL

MATING SIDE: AREA "F" 0.13µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL

COLOR OF HOUSING: GREY

COLOR OF HOUSING: GREEN

TOLERANCES NOT CUMULATIVE


THE NUMBER OF POSITION PER ROW HAS TO BE ADDED TO THE BASE NO. AS A DASH NO.
EG: 2-826634-0 = 20 POSITIONS

THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR FOR THE WEIGHT DETERMINATION
E.G: 20 X 0.1646 g = 3.292 g

OBSOLETE

C

B



SCALE 8:1
LAYOUT FOR HOLES ON PCB

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

SEE TABLE

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±0.2mm

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

-

DWN

G.HOLAUS

10NOV1989

CHK

SCHAARSCHMIDT M.

APVD

-

PRODUCT SPEC

108-18012

APPLICATION SPEC

114-25011

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT

SIZE

A2

CAGE CODE

00779

DRAWING NO

826629

RESTRICTED TO

-

SCALE

5:1

SHEET

4

OF

4

REV

AC1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-826629-2](#)