


(C) COPYRIGHT



		REVISIONS				
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
			W2	REVISED PER ECO-11-005140	31MAR11	HMR

130	183	165	318	4	4-87022-2	4
130	183	165	318	3	4	1
100	688	410	278	3	4-8	0
	628	350	278	5	3-8	9
	928	650	278	5	3-8	8
330	915	255	660	4	3-8	7
	533		278	5	3-8	6
430	1115		860	3	3-8	5
330	915		660	3	3-8	4
230	715		460	3	3-8	3
200	650	255	395	3	3-8	2
	828	550	278	5	3-8	1
100	688	410		4	3-8	0
100	863	585		3	2-8	9
100	663	385	278	3	2-8	8
280	815	255	560	4	2-8	7
100	533	255	278	4	2-8	6
100	533	255	278	3	2-8	5
100	608	330	278	3	2-8	4
335	835	165	670	4	2-8	3
100	562	284	278	6	2-8	2
	928	650		4	2-8	1
	828	550		4	2-8	0
	628	350		4	1-	9
	928	650		3	1-8	8
	828	550		3	1-	7
	628	350		3	1-8	6
100	443	165	278	7	1-9	5
	437	227	210	5	7-8	4
100	562	284	278	3	7-8	3
100	443	165		6	1-	1
	443	165		5	1-	0
100	443	165		4		9
	688	410		6	8	8
	508	230		6	8	7
100	1016	738		6	8	5
				5	8	4
100				4	8	3
100	1016	738		3		2
100	443	165	278	3	87022-7	
ID	C	IB	IA	FINISH	PART NO	

SEE 87878 FOR
ADDITIONAL PART NO'S

100	.793	.515	.278	3	9	8	9
	.660	.165	.495	5	9	8	-6
	.835	.165	.670	5	9	8	-5
100	1.238	.960	.278	6	9	8	-4
100	.828	.550	.278	6	9	8	-3
	.650	.255	.395	5	9	8	-2
	.728	.450	.278	5	9	8	-1
100	.728	.450		4	9	8	-0
	.863	.585		5	8	8	-9
	.663	.385		5	8	8	-8
100	.863	.585		4	8	8	-7
100	.663	.385		4	8	8	-6
	1.438	1.160		5	8	8	-5
100	1.438	1.160		4	8	8	-4
	1.238	.960		5	8	8	-3
100	1.238	.960	.278	4	8	8	-2
200	.560	.165	.395	3	8	8	-1
100	1.438	1.160	.278	3	8	8	-0
	1.238	.960		3	7	8	-8
	.738	.450		3	7	8	-3
	.928	.650		6	7	8	-1
	.628	.350	.278	6	7	8	-0
	1.056	.738	.318	3	6	8	-9
	.508	.230	.278	4	6	8	-7
100	.437	.227	.210	4	6		-6
	1.065	.165	.900	5	4	8	-4
	.483	.165	.318	5	4	87022	-3
ID	C	B	A	FINISH	PART NO.		

- | | | |
|----|---|------------|
| 1 | POINT OF MEASUREMENT FOR PLATING THICKNESS. | |
| 2 | CUSTOMERS APPLICATOR CUT-OFF DIMENSION. | SUPERSEDED |
| 3 | .00030 GOLD OVER .000050 NICKEL. | |
| 4 | .00015 GOLD OVER .000050 NICKEL. | |
| 5 | .000100-.000200 BRIGHT TIN-LEAD OVER .000050 NICKEL. | |
| 6 | .00050 GOLD OVER .00050 NICKEL. | |
| 7 | .00010 GOLD OVER .00050 NICKEL. | |
| 8 | OBSOLETE PART NO | |
| 9 | SUPERSEDED BY 87022-9 | |
| 10 | SUPERSEDED BY 3-104246-4 | |
| 11 | SUPERSEDED BY 4-87022-1 | |
| 12 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI | |
| 13 | OBSOLETE | |
| 14 | SUPERSEDED | |

SUPERSEDE BY 104842-2

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.

TOLERANCES ON:
DECIMALS $\pm .005$
ANGLES $\pm$

MATERIAL
PHOS. BRONZE

FINISH
SEE TABLE

CONTRACT NO

DR	<i>[Signature]</i>	6-21-88
CHK	<i>[Signature]</i>	24 JUN = 83
APPD	<i>[Signature]</i>	24 JUN = 83
APPD	<i>[Signature]</i>	6-24-83
DSGN APPD		
OTHER APPD		

TE Connectivity

NAME *POST, MOD II, .025 SQ,*
UNINSULATED

SIZE	FSCM NO	DRAWING NO
C	00779	87022

SCALE	#	SHEET	105
-------	---	-------	-----

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[87022-2](#)