


VERSAFIT-3X (3:1 RATIO)

Single Wall tube. A Commercial grade heat shrink tube primarily used for electrical insulation. Has a UL224 approval. Available in several colours.



PRODUCT DIMENSIONS


SIZE	Inside Diameter as supplied (min) mm (inch) D	Inside Diameter after recovery (max) mm (inch) d	Wall Thickness after recovery (nom) mm (inch) W	Wall Thickness Tolerance after recovery mm (inch)
1/8	3.2 (0.125)	1.1 (0.042)	0.58 (0.023)	0.08 (0.003)
1/4	6.4 (0.250)	2.2 (0.083)	0.58 (0.023)	0.08 (0.003)
3/8	9.5 (0.375)	3.2 (0.125)	0.61 (0.024)	0.08 (0.003)
1/2	12.7 (0.500)	4.3 (0.166)	0.61 (0.024)	0.08 (0.003)
3/4	19.1 (0.750)	6.4 (0.250)	0.61 (0.024)	0.08 (0.003)
1	25.4 (1.000)	8.5 (0.333)	0.64 (0.025)	0.08 (0.003)

VERSAFIT-3X (3:1 RATIO) – STANDARD
SIZE REFERENCE
DIMENSIONAL DRAWING



©2020 TE Connectivity Ltd. family of companies
All Rights Reserved

DIMENSIONS IN
mm (Inch)



TITLE

**VERSAFIT (3:1 RATIO) – IRRADIATED
MODIFIED POLYOLEFIN SINGLE WALL
HEAT SHRINK TUBING**

SHEET

NO

REV

REV ENGINEERING CHANGE CHK DATE

1 of 2

VERSAFIT-3X (3:1 RATIO) – Standard Sizes

A

VERSAFIT-3X (3:1 RATIO)

PRODUCT INFORMATION

General use single wall Polyolefin Tubing.
Shrink Ratio – 3:1
Longitudinal Shrinkage on full recovery – 0 to -15%
Material conforms to TE Specification RW-3009
Standard Colours: Black
Non-Standard Colours: Brown, Red, Orange, Yellow, Green, Blue, Violet, Grey, White
Flame Retardant

Tubing cut to specific lengths can be supplied from the product sizes
referenced within this drawing.

Cut length tolerances are as per the following table:

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
Up to 9.9mm	±0.5mm
10mm to 24.9mm	±1.0mm
25mm to 54.9mm	±1.5mm
55mm to 99.9mm	±3.0mm
100mm to 149.9mm	±4.0mm
150mm to 499.9mm	±5.0mm
500mm to 1200mm	±12.5mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[NB14644001](#)