



MODEL 4000A MEMS DC ACCELEROMETER

SPECIFICATIONS

- MEMS DC Accelerometer
- DC to 1300Hz Frequency Response
- Amplified Output, Signal Conditioned
- Temperature Compensated
- Economical, Light Weight

FEATURES

- $\pm 2g$ to $\pm 100g$ Dynamic Range
- High Over-Range Protection
- Gas Damped MEMS Sensors
- Low Power Consumption
- Screw Mounting
- 8 to 36Vdc Excitation Voltage

APPLICATIONS

- Low Frequency Monitoring
- Transportation
- Vibration Sensing
- Test & Instrumentation
- Machine Control
- Motion Analysis

The Model 4000A is an economical signal conditioned MEMS DC accelerometer packaged in an anodized Aluminum housing. The accelerometer is available in ranges from ± 2 to $\pm 100g$ with a wide bandwidth from DC to 1300Hz. The model 4000A accelerometers incorporate gas damped MEMS sensing elements that provide outstanding performance over an operating temperature range of -20°C to $+85^{\circ}\text{C}$.

The accelerometer is designed for 8 to 36Vdc excitation voltage and the signal conditioned output incorporates a 2.5V reference that offers the user an optional differential or single-ended output.

For a triaxial version, TE Connectivity also offers the model 4030 and 4630 accelerometers.

PERFORMANCE SPECIFICATIONS

All values are typical at +24°C, 80Hz and 12Vdc excitation unless otherwise stated. TE Connectivity reserves the right to update and change these specifications without notice.

Parameters

DYNAMIC

	±2	±5	±10	±20	±50	±100	Notes
Range (g)							
Sensitivity, Differential (mV/g)	1000	400	200	100	40	20	±10%
Frequency Response (Hz)	0-200	0-300	0-350	0-600	0-800	0-1300	±5%
Natural Frequency (Hz)	700	800	1000	1500	4000	6000	
Non-Linearity (%FSO)	±1	±1	±1	±1	±1	±1	
Transverse Sensitivity (%)	<3	<3	<3	<3	<3	<3	<1 Typical
Damping Ratio	0.7	0.7	0.7	0.7	0.6	0.5	
Shock Limit (g)	5000	5000	5000	5000	5000	5000	
Residual Noise (µV RMS)	500	300	300	350	400	350	Passband
Spectral Noise (µg/√Hz)	35	38	75	132	316	516	Passband

ELECTRICAL

Zero Acceleration Output (mV)	±100	Differential
Excitation Voltage (Vdc)	8 to 36	
Excitation Current (mA)	<5	
Bias Voltage (Vdc)	2.5	
Full Scale Output (differential)	±2 Vpk	
Full Scale Output (single-ended)	+0.5 to 4.5 Vpk	
Output Resistance (Ω)	<100	
Insulation Resistance (MΩ)	>100	@100Vdc
Turn On Time (msec)	<100	
Ground Isolation	Isolated from Mounting Surface	

ENVIRONMENTAL

Thermal Zero Shift (%FSO/°C)	±0.014	Typical
Thermal Sensitivity Shift (%/°C)	±0.028	Typical
Operating Temperature (°C)	-20 to 85	
Storage Temperature (°C)	-20 to 85	
Humidity	Epoxy Sealed	

PHYSICAL


Case Material	Anodized Aluminum
Cable	PFA Insulated Leads, Braided Shield, PU Jacket
Weight (grams)	7
Mounting	2x #4 or M3 Screws
Mounting Torque	3 lb-in (0.3 N-m)

Calibration supplied: CS-FREQ-0100 NIST Traceable Amplitude Calibration from 20Hz to ±5% Frequency Response Limit


Optional accessories: AC-D02652 Triaxial Mounting Block
121 3-Channel Precision Low Noise DC Amplifier

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. TE Connectivity reserves the right to make changes without further notice to any product herein. TE Connectivity makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does TE Connectivity assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. TE Connectivity does not convey any license under its patent rights nor the rights of others.



DIMENSIONS



SCHEMATIC



TYPICAL FREQUENCY AND PHASE RESPONSE



ORDERING INFORMATION

4000A	GGG	ZZZ
Range		
002=2g		
005=5g		
010=10g		
020=20g		
050=50g		
100=100g		
Cable length		
060 = 60 inches, 5 feet		
120 = 120 inches, 10 feet		
240 = 240 inches, 20 feet		
197 = 197 inches, 5 meters		
394 = 394 inches, 10 meters		

Example; 4000A-002-060
 Model 4000A, 2g range, 60inch (5ft) cable length

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Tel: 800-522-6752
customercare.hmp@te.com

EUROPE

MEAS France SAS
a TE Connectivity Company
Tel: +31 73 624 6999
customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Tel: 0400-820-6015
customercare.shzn@te.com

TE.com/sensorsolutions

MEAS France SAS and Measurement Specialties (China) , Inc., are TE Connectivity companies.

TE Connectivity, TE, TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2017 TE Connectivity Ltd. All Rights Reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4000A-002-060](#)