

NOTES:

MATERIAL:
HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.
TERMINAL: BRIGHT TIN PLATED, COPPER ALLOY.
SCREW: 6-32, STEEL, ZINC PLATED CLEAR CHROMATE.






ELECTRICAL:

UL CLASS	C:	20A, 150V.
UL CLASS	D:	10A, 300V.
CSA TYPE	B:	20A, 300V.
CSA TYPE	C:	20A, 300V.
CSA TYPE	D:	10A, 300V.
CSA TYPE	E:	20A, 300V.

WIRE RANGE: 12-22 AWG

MECHANICAL:
MAXIMUM TORQUE RATING: 7 IN-LBS.
RUNNING TORQUE: 0.5-3.5 IN-LBS UNLESS
OTHERWISE STATED.

- 1 SCREWS ARE BOTTOMED, NO THREAD INTERRUPT.
- 2 SCREWS ARE NICKEL PLATED BRASS.
- 3 SCREWS ARE CAPTIVE.
- 4 SEE FIGURE.
- 5 PRELIMINARY PART NUMBER.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 7 TERMINAL FINISH: MATTE TIN
- 8 OBSOLETE



2-796658-4

RUPT.	8 5	.160	4DB-P108-04-SPCL	1.365	4	3-796658-0
	8 5	.160	4DB-P108-03-SPCL	1.040	3	2-796658-9
	8	.160	4DB-P108-30	9.815	30	5-1437667-5
	8	.160	4DB-P108-29	9.490	29	796658-9
	8	.160	4DB-P108-28	9.165	28	5-1437667-3
	8	.160	4DB-P108-27	8.840	27	796658-8
	8	.160	4DB-P108-26	8.515	26	5-1437667-2
	8	.160	4DB-P108-25	8.190	25	796658-7
	8	.160	4DB-P108-24	7.865	24	5-1437667-0
	8	.160	4DB-P108-23	7.540	23	796658-6
	8	.160	4DB-P108-22	7.215	22	4-1437667-8
	8	.160	4DB-P108-21	6.890	21	796658-2
	8	.160	4DB-P108-20	6.565	20	4-1437667-6
	8	.160	4DB-P108-19	6.240	19	4-1437667-5
	8	.160	4DB-P108-18	5.915	18	4-1437667-4
	8 5 4	.160	4DB-P108-16-105	5.590	17	2-796628-4
	8	.160	4DB-P108-17	5.590	17	4-1437667-2
	8	.160	4DB-P108-16	5.265	16	4-1437667-0
	ING PER	8	.160	4DB-P108-15	4.940	15
2 1		.160	4DB-P108-14-102	4.615	14	2-796658-5
2		.160	4DB-P108-14-102	4.615	14	2-796658-3
		.160	4DB-P108-14	4.615	14	3-1437667-8
		.160	4DB-P108-13	4.290	13	3-1437667-7
		.160	4DB-P108-12	3.965	12	3-1437667-6
		.160	4DB-P108-11	3.640	11	3-1437667-5
		.160	4DB-P108-10	3.315	10	3-1437667-3
8 5 2		.160	4DB-P106-09-094	2.990	9	1-796658-7
		.160	4DB-P108-09	2.990	9	3-1437667-2
6 1 OBSOLETE		.160	4DB-P108-08-091	2.665	8	-1-796658-4
		.160	4DB-P108-08	2.665	8	3-1437667-1
8 5 3 2		.160	4DB-P106-07-100	2.340	7	2-796658-2
		.160	4DB-P106-07-093	2.340	7	1-796658-6
		.160	4DB-P108-07	2.340	7	3-1437667-0
8 5 3 2		.160	4DB-P106-06-099	2.015	6	2-796658-1
6 1 OBSOLETE		.160	4DB-P108-06-090	2.015	6	-1-796658-3
8 5		.200	4DB-P108-06	2.015	6	2-796658-6
		.160	4DB-P108-06	2.015	6	2-1437667-9
8 5 3 2	.160	4DB-P106-05-098	1.690	5	2-796658-0	
6 4 OBSOLETE	.160	4DB-P108-05-093	1.690	5	-1-796658-5	
	.160	4DB-P108-05	1.690	5	2-1437667-8	
8 5 3 2	.160	4DB-P106-04-097	1.365	4	1-796658-9	
1	.160	4DB-P108-04-089	1.365	4	1-796658-2	
	.160	4DB-P108-04	1.365	4	2-1437667-6	
8 5 3 2	.160	4DB-P106-03-096	1.040	3	1-796658-8	
6 1	.160	4DB-P108-03-088	1.040	3	-1-796658-1	
	.160	4DB-P108-03	1.040	3	2-1437667-5	
7	.142	4DB-P108-02-143	.715	2	2-796658-8	
	.142	4DB-P108-02-142	.715	2	2-796658-7	
	.160	4DB-P108-02	.715	2	2-1437667-4	
	DIM B	CATALOG NUMBER	DIM A	NO OF POS.	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S WELDON	01MAY2003		 TE Connectivity	
		CHK S YODER	5/1/03			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S YODER	5/1/03		NAME	
	0 PLC ± -	PRODUCT SPEC	ASSEMBLY, DUAL BARRIER			
	1 PLC ± -	—	4DB P108 XX			
	2 PLC ± .01	APPLICATION SPEC				
	3 PLC ± .005	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	4 PLC ± -	WEIGHT	A2	00779	C-2-1437667-4	—
	ANGLES ± 1°	—				
MATERIAL	FINISH	CUSTOMER DRAWING		SCALE	SHEET	REV
—	—			NTS	1 of 1	N8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4DB-P108-08](#)