


REV. B
DCO 300825

TOLERANCES $\pm .010"$ - UNLESS
OTHERWISE SPECIFIED

COIL: @ 25°C
RESISTANCE 1275 OHMS $\pm 10\%$
NOMINAL VOLTAGE 48 VDC
MUST OPERATE 24.0 VDC MAX.
TRANSIENT SUPPRESSION - 42 VDC MAX.
MUST RELEASE 10.0 VDC MAX., 3.0 VDC MIN.

ENVIRONMENT:
VIBRATION 70 Hz TO 3000 Hz @ 30 g's
SHOCK 200 g's 6 MS. DURATION
TEMPERATURE -70 °C TO +125 °C
NOTES: OPERATE, RELEASE 6 MS MAX.
CONTACT STABILIZATION 2.5 MS MAX.
CONTACT BOUNCE 1 MS MAX.
CONTACT BREAK BOUNCE 0.1 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL
5 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE
100,000 OPERATIONS

DR. B.D. 25APR2008 CK. 5/9/08 J.M.B.

Tyco Electronics

©COPYRIGHT 2005
TYCO ELECTRONICS CORPORATION
ALL INTERNATIONAL RIGHTS RESERVED

CUST. M83536/6-028M
CUST. NO. ---- REV. ---

TE NUMBER
8-1617760-7

CII PART NUMBER
FCB-405-0628M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[FCB-405-0628M](#)