

REV. 1  
DCO 16124


COIL: @ +25 °C  
 RESISTANCE 27 OHMS ± 10%  
 NOMINAL VOLTAGE 5.0 VDC  
 MUST OPERATE 2.7 VDC  
 MUST RELEASE 1.65 VDC MAX, 0.29 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 100 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX  
 CONTACT STABILIZATION 2.5 MS MAX  
 ALL OTHER REQUIREMENTS TO MIL-R-39016 LEVEL M

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO  
 2 AMPS 28 VDC RESISTIVE  
 100,000 OPERATIONS

DR. R.B. 3/11/99 CK. Gg/H z/21/00

**COMMUNICATIONS**  
 INSTRUMENTS, INC.

CUST. QPL  
 CUST. NO. M39016/6-139M

TYPE "HFW" RELAY

HFW1201L01M

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[M39016/6-139M](#)