

COIL: @ +25 °C

RESISTANCE 160 OHMS ± 10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 7.2 VDC

MUST RELEASE 0.7 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 100 g's 6 ± 1 MS. DURATION

TEMPERATURE -65 °C TO +125 °C


NOTES: MAXIMUM TRANSIENT SUPPRESSED VOLTAGE OF -24 VDC WITH BIFILAR COIL

OPERATE & RELEASE 5 MS MAX

CONTACT BOUNCE 2 MS MAX

CUSTOMER DATA SHEET

BLUE BEAD



CONTACT RATING: LOW LEVEL TO 2A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 9/27/94 CK. 9/27/94

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. OPL
CUST. NO. M39016/22-016L

TYPE "HMB" RELAY

HMB1201G01L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HMB1201G01L](#)