

REV. 1 4/26/95

COIL: • +25 °C
 RESISTANCE 160 OHMS ± 10%
 NOMINAL VOLTAGE 12.0 VDC
 MUST OPERATE 7.2 VDC
 MUST RELEASE 4.0 VDC MAX, .7 VDC MIN.


ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS • 30 g's
 SHOCK 100 g's 6 ± 1 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: MAXIMUM TRANSIENT SUPPRESSED VOLTAGE
 OF -24 VDC WITH BIFILAR COIL
 OPERATE & RELEASE 5 MS MAX.
 CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET

BLUE BEAD 7



CONTACT RATING: LOW LEVEL TO 2A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 5/27/94 CK. 4/26/95

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. OPL
 CUST. NO. M39016/22-016P

TYPE "HMB" RELAY

HMB1201G01P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HMB1201G01P](#)