

COIL: @ 25°C

RESISTANCE 1030 Ω ± 10%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 11.4 VDC

MUST RELEASE 6.9 VDC MAX, 1.1 VDC MIN.

ENVIRONMENT:


VIBRATION 10 CPS TO 2500 CPS @ 20 g's

SHOCK 50 g's 6 MS.DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES:

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2 AMPS RESISTIVE 100,000 OPERATIONS

DR. R.B. 9-19-90 CK. 9/19/90 *[Signature]*



Communications
Instruments, Inc.

CUST. QPL
CUST. NO. M39016/44-028P

TYPE HMS RELAY

HMS1130S04P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HMS1130S04P](#)