

REV. 1 10/4/96

COIL: @ 25°C  
 RESISTANCE 47 OHMS  $\pm$  10%  
 NOMINAL VOLTAGE 5.0 VDC  
 MUST OPERATE 2.2 VDC  
 MUST RELEASE 0.21 VDC

ENVIRONMENT:


VIBRATION 10 CPS TO 2500 CPS @ 20 g's  
 SHOCK 50 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 6 MS MAX.

RELEASE TIME 5 MS MAX.

CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A  
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 10/2/91 CK 10/4/96

COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. QPL  
 CUST. NO. M39016/44-004M

TYPE "HMS" RELAY

HMS1131S01M

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HMS1131S01M](#)