


COIL: @ 25°C
 RESISTANCE 2000 OHMS \pm 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE VOLTAGE 14.4 VDC
 TURN-ON BASE CURRENT 0.10 mADC
 MUST RELEASE 8.0 VDC MAX, 1.25 VDC MIN.

CUSTOMER DATA SHEET

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: TURN-ON TIME 2.0 MS MAX
 TURN-OFF TIME 7.5 MS MAX
 CONTACT STABILIZATION TIME 2.0 MS MAX



CONTACT RATING: LOW LEVEL TO 1A
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 7/23/98 CK EEPY 7/23/98

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M28776/5-036P

TYPE J1MAT RELAY

J1MACT-26XPS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[J1MACT-26XPS](#)