

REV. 0

DCO 142549

COIL: @ 25°C  
 RESISTANCE 50 OHMS  $\pm$  10%  
 NOMINAL VOLTAGE 5.0 VDC  
 MUST OPERATE 2.7 VDC


MUST RELEASE 1.4 VDC MAX. 0.22 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX.  
 RELEASE TIME 4.0 MS MAX.  
 CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A  
 28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 12/12/00

CK. 12/12/00

**CII Technologies**  
 advanced control electronic solutions

CUST. QPL  
 CUST. NO. M39016/15-082M REV.

JMAD RELAY

JMACD-5XM

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMACD-5XM](#)