

REV. 0
DCO 143202


COIL: @ 25°C
RESISTANCE 1600 OHMS \pm 10%
NOMINAL VOLTAGE 18.0 VDC
MUST OPERATE 9.8 VDC
MUST RELEASE 6.0 VDC MAX., 0.92 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
SHOCK 75 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX.
RELEASE TIME 2.0 MS MAX.
CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
1A 28 VDC RESISTIVE 100,000
OPERATIONS

DR. ASB 9/07/01

OK 9/7/01

CI Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/11-048P REV.

"JMS" RELAY

JMSC-18XPS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMSC-18XPS](#)