

REV. 0  
DCO 142074

COIL: @ 25°C  
RESISTANCE \_\_\_\_\_ 100 OHMS  $\pm$  10%  
NOMINAL VOLTAGE \_\_\_\_\_ 5.0 VDC  
MUST OPERATE \_\_\_\_\_ 2.6 VDC


MUST RELEASE \_\_\_\_\_ 1.4 VDC MAX, 0.23 VDC MIN.

#### ENVIRONMENT:

VIBRATION \_\_\_\_\_ 10 CPS TO \_\_\_\_\_ 3000 CPS @ \_\_\_\_\_ 30 g's  
SHOCK \_\_\_\_\_ 75 g's \_\_\_\_\_ 6 MS. DURATION  
TEMPERATURE \_\_\_\_\_ -65 °C TO \_\_\_\_\_ +125 °C

NOTES: \_\_\_\_\_ OPERATE TIME 4.0 MS MAX  
\_\_\_\_\_ RELEASE TIME 7.5 MS MAX  
\_\_\_\_\_ CONTACT BOUNCE 1.5 MS MAX

#### CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: \_\_\_\_\_ LOW LEVEL TO 1A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 6/6/00

CK. LERRY 6/6/00

COMMUNICATIONS  
INSTRUMENTS, INC.

CUST. \_\_\_\_\_ QPL  
CUST. NO. M39016/16-017L REV. \_\_\_\_\_

\*JMSD\* RELAY

JMSWD-5XL

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMSWD-5XL](#)