


COIL: @ 25°C  
 RESISTANCE 3300 OHMS  $\pm$  10%  
 NOMINAL VOLTAGE 26.5 VDC  
 MUST OPERATE 14.0 VDC  
 MUST RELEASE 8.0 VDC MAX. 1.4 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4 MS MAX  
RELEASE TIME 2.0 MS MAX  
CONTACT STABILIZATION TIME 2.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 9/23/96 CK 9/23/96

**COMMUNICATIONS  
INSTRUMENTS, INC.**

CUST. QPL  
 CUST. NO. M39016/11-023P

TYPE "JMS" RELAY

**JMSW-26XP**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMSW-26XP](#)