




COIL: @ 25°C

RESISTANCE 90 OHMS ± 10%

NOMINAL VOLTAGE 6.0 VDC

MUST OPERATE 3.0 VDC

MUST RELEASE 0.3 VDC

ENVIRONMENT:


VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 ± 1 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE TIME 4 MS MAX.
CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
1 AMP 28 VDC RESISTIVE
100,000 OPERATIONS

DR. R.B. 9/7/95 CK. 9/11/95

**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. C.I.I. STD.

CUST. NO.

TYPE "MFW" RELAY

MFW1201G00

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MFW1201G00](#)