

REV. 0

DCO 143609

COIL: @ 25°C

RESISTANCE 3200 $\Omega \pm 10\%$

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 14.0 VDC

MUST RELEASE 1.4 VDC

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 7.5 MS MAX

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. ASB 10 JUL 02

7/10/02

CII Technologies
advanced control electronic solutions

CUST. C.I.I. STD.

CUST. NO. REV.

"MGSD" RELAY

MGSPD-26W

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[MGSPD-26W](#)