



P700

SPECIFICATIONS

- ◆ **Rugged Design for Harsh Environments**
- ◆ **Versatile Packaging Design**
- ◆ **Low and High Level Output Signals**
- ◆ **Intrinsic Safety Approval to Ex ia IIc T4**
- ◆ **High Overpressure Capability**

P700 series pressure transducers are designed for high reliability and stability. The all welded construction incorporates a double cantilever beam with bonded foil strain gauges. Coupling to the pressure diaphragm via a force rod, gives excellent thermal isolation from the fluid or gas being measured. High overload protection is an integral part of the design. These units are capable of sensing extremely small changes of applied pressure and are relatively insensitive to vibration, altitude and shock.

For parts requiring RoHS compliance, please contact factory.

FEATURES

- ◆ Low and High Level Output
- ◆ All Welded Construction
- ◆ High Pressure Overload Protection
- ◆ Pressure Ranges 0-10,000 PSI (0.7 to 700 bars)
- ◆ 2 Wire 4-20 mA Option BASEEFA and Cenelec Approval Class Ex ia IIc T4

APPLICATIONS

- ◆ Hydraulic Pressure Monitoring
- ◆ Torpedo Depth Sensing
- ◆ Vehicle Brake System Monitoring
- ◆ Military and Commercial Aircraft

PERFORMANCE SPECS

Low Level Output			
Model Number	P711/9	P721/4	P701/9
Input Supply	10VDC/AC RMS	10VDC/AC RMS	10VDC/AC RMS
Voltage (Max)	12V	12V	12 V
Impedance (ohms)	350	350	350
Current	±5%	±5%	±5%
	-	-	-
Output at +25°C			
Full Range Output with 1 metre cable	25mV, ±2%	25mV, ±2%	25mV, ±1%
Impedance (ohm)	350, ±5%	350, ±5%	350, ±5%
Current (mA max)	-	-	-
Residual Unbalance % F.R.O.	< ± 2	< ± 2	< ± 1
Accuracy			
Combined Non-Linearity (Typical)	± 0.2	± 0.2	± 0.18
Hysteresis and Non Repeatability % F.R.O. (Max)	± 0.2	± 0.5	± 0.3
Combined Thermal M.R.	± 0.03	± 0.03	± 0.02
Zero and Sensitivity Error %F.R.O./ °C H.R.	± 0.03	± 0.03	± 0.015
Physical			
Max. Height (L/mm)	64.4	64.4	64.4
Cable version (mm/in.)	83/3.27	83/3.27	83/3.27
Connector version (mm/in.)	83/3.27	83/3.27	83/3.27
Weight (gm)	230	230	230

PERFORMANCE SPECS (CONT)

High Level Output					
Model Number	P741/9	P751/9	P761/9	P781/9	P791/9
Input Supply					
Voltage (Max)	10VDC/AC RMS	11-18VDC	18-32VDC	10-36VDC	15VDC
Impedance (ohms)	12 V max	-	-	-	-
Current	30-35mA	20-40mA	30-40mA	-	30mA
Output at +25°C					
Full Range Output with 1 metre cable	5V ±1%	2.5V ±1%	5V ±1%	4-20 mA	5.0 ±1%
Impedance (ohm)	<10 ohm	<10 ohm	<10 ohm	Load Resist. 1.0 k max. at 36VDC	<10 ohm
Current (mA max)	5	5	5	-	5
Residual Unbalance % F.R.O.	< ± 1	< ± 2	< ± 1	1 < ± 1	< ± 1
Accuracy					
Combined Non-Linearity (Typical)	± 0.18	± 0.18	± 0.18	± 0.18	± 0.18
Hysteresis and Non Repeatability % F.R.O. (Max)	± 0.25	± 0.25	± 0.25	± 0.25	± 0.25
Combined Thermal M.R.	± 0.02	± 0.02	± 0.02	± 0.02	± 0.02
Zero and Sensitivity Error %F.R.O./°C H.R.	± 0.015	± 0.015	± 0.015	± 0.015	± 0.015
Physical					
Max. Height (L/mm)	91.6	91.6	91.6	91.6	91.6
Cable version (mm/in.)	99/3.90	114/4.49	114/4.49	129/5.07	99/3.90
Connector version (mm/in.)	99/3.90	114/4.49	114/4.49	129/5.07	99/3.90
Weight (gm)	250 gm	250 gm	250 gm	250 gm	250 gm

COMMON SPECIFICATIONS

Pressure Ranges	Gauge or absolute reference
High (psi)	0-75, 100, 150, 200, 250, 350, 500, 750, 1000, 1500, 2000, 2500, 3500, 5000, 7500, 10,000
(bar)	0-5, 0, 7, 10, 15, 20, 25, 35, 50, 70, 100, 150, 200, 250, 350, 500, 700
Medium (psi)	0-10, 15, 20, 25, 35, 50
(bar)	0-0.7, 1.0, 1.5, 2.0, 2.5, 3.5
DIN (bar)	0.6, 1, 1.6, 2.5, 4, 6, 10, 16, 25, 40, 60, 100, 160, 250, 400, 600
Pressure Limit	<5x full range pressure or 12,000 psi whichever is less
Burst Pressure	>10x full range pressure or 20,000 psi whichever is less
Pressure Media	Liquids or gases compatible with 17-4 PH and 17-7 PH stainless steel or Inconel 625
Shunt Calibration	80% ±5% full range pressure
Residual Unbalance	<±1% F.R.O. P700 <±2% F.R.O. P720
Temperature Range	
Operable	-65°F to 250°F (-54°C to 120°C)
Compensated	32°F to 212°F (0°C to 100°C)
Humidity	
Plug Outlet	95% Relative humidity
Cable Outlet	Immersible to 1000 feet
Acceleration Response	< 0.10% F.R.O./g (Medium range) <0.02% F.R.O./g (High range)
Natural Frequency	Approx 2.5 kHz for 10 psi to approx 40 kHz for 10,000 psi
Insulation Resistance	500 MOhm at 50 VDC

1. A low current consumption version is available (1000 ohm bridge) at extra cost.

CONNECTIONS

CONNECTIONS:

CABLE CONNECTIONS

RED* PIN A* EXCITATION (+)

WHITE PIN D EXCITATION (-)

YELLOW PIN B OUTPUT (+)

BLUE* PIN C* OUTPUT (-)


VIOLET PIN E

GREY PIN F


} 80% Shunt calibration

* 2 - Wire transmitter connections


0 Volt P791/4



6 way bayonet
hermetically sealed
MII - C 26482
shell size 10



ORDERING INFORMATION



NOTE: Unit comes standard with 1 meter of cable.

For a different cable length, add 2 digits "xx" to the end of the configuration above indicating the length desired. Max 20 meters.

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Phone: 800-522-6752
Email: customercare.fimt@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Phone: 800-440-5100
Email: customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Phone: 0400-820-6015
Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[P781-0004-100BAV](#)