

TIP SENSITIVE BEARING THERMOCOUPLE PROBE

Temperature Sensor

Specifications

- Variety of Configurations
- Cut-To-Length
- Fast Response
- Tip Sensitive
- Single and Dual Junctions
- Custom Designs Available

The Tip Sensitive Bearing Thermocouple Probe is a tubular sensor in which the sensing junction is encased in a copper alloy tip. This allows for increased accuracy and sensitivity to temperature changes at the point of contact in bearings. Inserted at an opening on the bearing housing, they are used in electric motors and generators for continuous sensing of the bearing temperature.

Bearing sensors can be used with a fluid sealed adjustable spring loaded holder for proper loading in any depth hole to maintain contact with the bearing surface.

Features

- Sheath Styles:
 - » Stainless Steel, Isolated Stainless Steel, Insulated Epoxy Glass
 - » Copper Tip
- Junction Types, Single and Dual:
 - » J, K, T, E
 - » Grounded or Ungrounded
- Sheath Diameters:
 - » 0.188", 0.250", 0.215"
- Leadwire/Cable Options

Applications

- Electric Motors
- Generators

TIP SENSITIVE BEARING THERMOCOUPLE PROBE

Temperature Sensor

Performance Specifications

Insulation Resistance – Ungrounded Model:

1,000 megohms @ 500 V, leads to case

Vibration:

Withstands 5 to 500 Hz at 3 g-level peak for 3 hours. Per ASTM E 644, Sec. 10.

Shock:

Withstands 50 g-level peak sine wave shock of 11 milliseconds duration. Per ASTM E 644, Sec. 11

Pressure Rating:

Standard Stainless Steel Sheath: 100 psi (6.9 bar)

Isolated Stainless Steel Sheath: 100 psi (6.9 bar)


Insulated Epoxy Glass Sheath: 30 psi (2.1 bar)

Fluid Seal Holder: 50 psi

Thermocouple Temperature Accuracy Specifications:

Type	Temp Range	Standard Limits of Error	Special Limits of Error
T	-200 to 0°C	±1°C or 1.5%	Not ASTM Defined
	0 to 350°C	±1°C or 0.75%	±0.5°C or 0.4%
J	0 to 750°C	±2.2°C or 0.75%	±1.1°C or 0.4%
E	-200 to 0°C	±1.7°C or 1%	Not ASTM Defined
	0 to 900°C	±1.7°C or 0.5%	±1°C or 0.4%
K	-200 to 0°C	±2.2°C or 2%	Not ASTM Defined
	0 to 1,250°C	±2.2°C or 0.75%	±1.1°C or 0.4%

Dimensions



TIP SENSITIVE BEARING THERMOCOUPLE PROBE

Temperature Sensor

Ordering Information

Tip Sensitive Bearing Thermocouple Probe			
Model	Sheath Style	Temperature Range	Minimum / Maximum Lengths
410A	Insulated Epoxy Glass	-50 to 155°C (-58 to 311°F)	3.0" Minimum / 48.0" Maximum
410B	Standard Stainless Steel	-50 to 250°C (-58 to 482°F)	3.0" Minimum / 96.0" Maximum
410C	Isolated Stainless Steel	-50 to 250°C (-58 to 482°F)	5.0" Minimum / 96.0" Maximum
Model	Thermocouple Type	Junction	Color Code
J	J	Single	Red/White [Constantan/Iron]
K	K	Single	Red/Yellow [Alumel/Chromel]
T	T	Single	Red/Blue [Constantan/Copper]
E	E	Single	Red/Purple [Constantan/Chromel]
JJ	JJ	Dual	Red/White // Red/White
KK	KK	Dual	Red/Yellow // Red/Yellow
TT	TT	Dual	Red/Blue // Red/Blue
EE	EE	Dual	Red/Purple // Red/Purple
Model	Junction Style		
G	Grounded Junction		
U	Ungrounded Junction		
Model	Limits of Error		
A	Standard Limits of Error		
B	Special Limits of Error		
Model	'L' Sheath Length		
----	Define 'L' Length in Inches (See above for Minimum / Maximum Lengths) Example: 10.0 = 10.0"; 6.3 = 6.3"		
Model	'D' Sheath Diameter		
B	.188" Diameter		
C	.250" Diameter (Standard SS and Isolated SS Only)		
D	.215" Diameter		
Model	'Y' Leadwire/Cable Options		
N	No Options, Solid TFE Leadwires (36.0" Standard)		
W	Leadwire Options		

Stocked Part Numbers*

Model Number

410C T U A 36.0 B W=10.0" Leads
410C E U A 36.0 B W=10.0" Leads
410C J U A 36.0 B W=10.0" Leads
410C K U A 36.0 B W=10.0" Leads

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
1711 139th Lane NW
Andover, MN 55304
Tel +1 763 689 4870
Fax +1 763 689 5033
temp.eng.us@meas-spec.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
4 Rue Gaye Marie
31027 Toulouse, France
Tel +33 (0) 582 082 200
Fax +33 (0) 582 082 151

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
No. 26 Langshan Road
Shenzhen High-Tech Park (North)
Nanshan District, Shenzhen 518057 China
Tel +86 755 3330 5088
Fax +86 755 3330 5099

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[R-10318-69](#)