

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.

DWG NO 565504-3
THIS DRAWING IS A CONTROLLED DOCUMENT.


USED ON —

APPLICATOR PARTS LIST				TYPE HINGEBAR — MARK III										
NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA			TERMINALS			
1	⚠ WIRE CRIMPER	1	471788	42	FRONT STABILIZER BAR	1	811006-1	TO APPLY TERMINAL			.018 BRASS	TE P/N	MFG P/N	
2	⚠ INS. CRIMPER	1	472123	43	—	—	—	.018 STK .016 STK			41531	1949687	SFO-61T-250A	
3	⚠ ANVIL	1	388623	44	HINGE BLOCK & STABILIZER	1	810974-1	WIRE SIZE	CRIMP HEIGHT	C.H.	41532			
4	⚠ ANVIL INSERT	1	811045-1	45	HINGE PIN	1	811007-1	18	.052	.048	41799			
5	⚠ SHEAR BLADE	1	810412	46	—	—	—	16	.056	.052	41800			
6	⚠ REAR SHEAR PLATE	1	811067-1	47	HINGE BAR ASSY	1	565062-1	14	.062	.060	41801			
7	⚠ SHEAR BLADE SPRING	1	810410-1	48	HINGE BAR SPRING	2	3-23846-5	12	.072	.070	41802			
8	⚠ FRONT SHEAR PLATE	1	388632-2	49	STRIP GUIDE STOP	2	810417	—	—	—	42041			
9	REAR ANVIL SPACER PL	—	—	50	STRIP HOLD DOWN	1	810411	CRIMP	SIZE	TYPE	FEED	42144		
10	FRONT ANVIL SPACER PL	—	—	51	SPACER-COMPRESSION SPR	2	811070-1	WIRE	.160	TAB LOC	.770	42482		
11	TOOL SPACER	—	—	52	CAM FOLLOWER HOLDER	1	810409	INSUL.	.220	"O"		60645		
12	CRIMP SPACER	1	681154-1	53	CAM FOLLOWER	1	24746-1	SLEEVED	—	—		61156		
13	FRONT STRIP GUIDE	1	811052-1	54	SPRING BRACKET	1	810418	INSULATION RANGE		WIRE RANGE		—		
14	REAR STRIP GUIDE	1	388621-1	55	⚠ CAM FOLLOWER SPRING	1	810408	.210-.250		18-12		—		
				56	HOOK HOLDER	1	810419	EXPLODED VIEW					—	
15	RAM	1	473828	57	⚠ SHEAR PICK-UP HOOK	1	810416	A-6004-3 A-6004-4 AI-8011					—	
16	RAM RETAINING PLATE	1	465004-2	58	HOLD DOWN-HINGE BAR	1	811009-1	REMARKS:END OF WIRE APPLICATION			.016 STEEL			
17	ADJ. PLATE	1	811010-1	59	DEPRESSOR SCREW	1	810642-1	TERM APPL SPEC 114-2078					42404	
18	PROTECTIVE PLUG	1	23141-3	60	WASHER	4	376482	⚠ RECOMMENDED SPARE PARTS					1742460	
19	APPLICATOR MOUNT ASSY.	—	—	61	⚠ FEED FINGER SPRING	1	810421-1	2. FOR HARDWARE: SEE 687520-1						
20	BASE PLATE	1	465238-1	62	DOWEL PIN	2	1-21030-5	—					—	
21	BASE BLOCK	—	—	63	MICRO-SWITCH	1	23496-1	—					.016 BRASS	
22	STRIP GUIDE PLATE	—	—	64	MICRO-SWITCH COVER	1	22689-2	—					42511	
23	⚠ ANVIL HOLDER	1	810423	65	BRACKET, MICRO-SWITCH	1	811074-1	—					42742	
24	AUX. ANVIL HOLDER	—	—	—			—					60020		
25	STRIPPER	—	—	66	CONNECTOR	1	22787-2	—					60641	
26	STRIPPER MOUNT	—	—	67	HOOK HOLDER SCREW	1	810413	—					60712-1	
27	RETAINER PLATE	—	—	68	—	—	—	—					150561	
28	STRIPPER MOUNT BRACKET	—	—	69	SPACER, ANVIL HOLDER	1	811223-1	—					63445	
29	STRIPPER BUSHING	—	—	70	LEAD WIRE ASSY	1	465918-1	—					—	
30	STOCK DRAG	1	811063-2	71	DOWEL PIN	1	465702-1	THIS APPLICATOR IS TO BE USED ON					—	
31	STOCK DRAG HANDLE	—	—	72	PLATE, I.D.	1	452373-1	AMP-O-LECTRIC 1-471273-3					—	
32	STOCK DRAG STUD	—	—											
33	STOCK DRAG SPRING	2	810135											
34	STOCK DRAG ADJ. SCREW	—	—											
35	FEED FINGER HOLDER	1	810131											
36	FEED FINGER	1	810422											
37	⚠ FEED FINGER TIP	1	810420											
38	FEED FINGER STUD	1	810414-1											
39	BASE CASTING	1	570238											
40	GUARD ASSY	1	457698-4											
41	—	—	—											
								DWN			2855800		MATERIAL	

LOC
A
DIST
4

	Z4	ECR-09-020706	9-2009	MY	GB
P	LTR	REVISION RECORD	DATE	DWN	APVD

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC	± —
		1 PLC	± —
		2 PLC	± —
		3 PLC	± —
		4 PLC	± —
ANGLES ±		—	
SURFACE TEXTURE			

DWN M.YOUNGER		28FEB00	MATERIAL — —		HEAT TREAT — —		
CHK M.YOUNGER		28FEB00	<div> Tyco Electronics</div> <div>Tyco Electronics Corporation Harrisburg, PA 17105-3608</div>				
APVD T.ELBIN		28FEB00					
NAME HINGEBAR — MARK III —							
SCALE —	SIZE A3	DRAWING NO 565504-3			SHEET 1	OF 1	REV Z4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[565504-3](#)