

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

DS

O

RELEASED(FC00-0069-04)

13/APR/'04

BH

CS

0.5 MAX CUT OFF TAB

0.5 MAX CUT OFF TAB

15.9 MAX

12.3

6.3

5.6

6.8

3.8

1.6

1.65

TRADE MARK

MATE WITH 0.8T TAB

VMA

7 REF

8.8 MAX

PRE-TIN BRASS

1743058-1

MATERIAL

PART NUMBER

WIRE RANGE AWG#22~#16

INSULATION DIA

0.3~1.42mm²

ø1.7~4.32mm

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DWN: BH CHD

CHK: BV KANG

APVD: CS LEE

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

DIMENSIONS:
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 <XX<10 ± 0.2
10 <XX<30 ± 0.25
30 <XX ± 0.3
ANGLES ± 3°

3rd ANGLE PROJECTION

MATERIAL

SEE TABLE

FINISH

tyco
ElectronicsAMP KOREA.
kyungsan, korea

NAME

187 SERIES FLAG POSITIVE LOCK
EX RECEPTACLE FOR 0.8T TAB

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=

1743058

SCALE 1/1

SHEET 1 OF 1

REV 0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1743058-1](#)