








© COPYRIGHT

		REVISIONS				
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
			K1	REVISED PER ECO-11-005294	06APR11	HMR



1. 0.010 MAX CUT-OFF TAB FOR LOOSE PIECE.
2. GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000015 GOLD ON CONTACT AREA
3. GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT .000030 GOLD ON CONTACT AREA.
4. .000016 MIN TIN.
5. LUBRICATED
6. .000100-.000200 BRIGHT TIN OVER .000030 NICKEL.
7. POINT OF MEASUREMENT FOR PLATING THICKNESS.
8. .000015 GOLD ON CONTACT AREA. .000050-.000100 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
9. .000030 GOLD ON CONTACT AREA. .000050-.000100 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
10. OBSOLETE PART NUMBER

9	10	102104-6	102100-9/10
8	10	102104-5	102100-8/10
6	5	10102104-4	10102100-6
4	5	102104-3	102100-5
3		102104-2	102100-2
2		102104-1	102100-1
FINISH	LOOSE PIECE PIN	PART NO	

		FINISH		LOOSE PIECE P/N		PART NO	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm .005$ ANGLES $\pm$		CONTRACT NO		 TE Connectivity NAME CONTACT, MOD I, RECEPTACLE, CRIMP SNAP-IN, HIGH PRESSURE, #18 - #22AWG, SIDE FEED			
		DR					
		CHK					
		APPD					
MATERIAL PHOS. BRONZE		APPD					
FINISH SEE TABLE		DSGN APPD		SIZE		CODE IDENT NO	
		OTHER APPD		C		00779	
				SCALE		DRAWING NO	
						102100	
						SHEET	

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[102100-2](#)