


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	W1	PART STATUS UPDATED IN PART LIST TABLE	07FEB2018	SD	PS

D

C

B

A



STANDOFFS: UP TO 9 POS-(2 REQD) ON THE OUTSIDE ENDS OF THE HOUSING
10 TO 19 POS-(3 REQD) TWO ON THE OUTSIDE ENDS AND ONE CENTERED
ON THE HOUSING. 19 POS AND LARGER-(4 REQD) TWO ON THE OUTSIDE ENDS
AND TWO SPACED EVENLY WITHIN THE REMAINING LENGTH OF THE HOUSING.



POINT OF MEASUREMENT FOR PLATING THICKNESS.



FOR 3 POS (3--4 & 3--9 ONLY) ONE SLOT, .215 WIDE.



INDICATED PARTS ARE PACKAGED IN "GANG-OF-TUBES".



RECESSED DATE CODE



INDICATED PARTS ARE PACKAGED IN "SINGLE TUBES".



.000015 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD
ON THE SOLDER TAIL, ALL OVER .000050 NICKEL.



.000015 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN
ON THE SOLDER TAIL, ALL OVER .000050 NICKEL.



PRELIMINARY PART



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

D

C

B

A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

		₉ ₁₀	OBSOLETE	₈	1.720	1.640	1.500	15	16	4-102203-0
SUPERSEDED BY 8-102203-4				₈	.420	.340	.200	2	₃ 3	3-102203-9
		₉ ₁₀	OBSOLETE	₈	1.020	.940	.800	8	9	3-102203-8
SUPERSEDED BY 5-102203-1				₈	.520	.440	.300	3	4	3-102203-7
		₆ ₁₀	OBSOLETE	₇	.820	.740	.600	6	7	3-102203-6
SUPERSEDED BY 103361-8				₇	1.120	1.040	.900	9	₄ 10	3-102203-5
				₇	.420	.340	.200	2	₃ 3	3-102203-4
			OBSOLETE	₇	3.720	3.640	3.500	35	36	3-102203-3
			OBSOLETE	₇	3.620	3.540	3.400	34	35	3-102203-2
			OBSOLETE	₇	3.520	3.440	3.300	33	34	3-102203-1
			OBSOLETE	₇	3.420	3.340	3.200	32	33	3-102203-0
			OBSOLETE	₇	3.320	3.240	3.100	31	32	2-102203-9
			OBSOLETE	₇	3.220	3.140	3.000	30	31	2-102203-8
			OBSOLETE	₇	3.120	3.040	2.900	29	30	2-102203-7
			OBSOLETE	₇	3.020	2.940	2.800	28	29	2-102203-6
			OBSOLETE	₇	2.920	2.840	2.700	27	28	2-102203-5
			OBSOLETE	₇	2.820	2.740	2.600	26	27	2-102203-4
			OBSOLETE	₇	2.720	2.640	2.500	25	26	2-102203-3
		₁₀	OBSOLETE	₇	2.620	2.540	2.400	24	25	2-102203-2
				₇	2.520	2.440	2.300	23	24	2-102203-1
		₁₀	OBSOLETE	₇	2.420	2.340	2.200	22	23	2-102203-0
				₇	2.320	2.240	2.100	21	22	1-102203-9
		₁₀	OBSOLETE	₇	2.220	2.140	2.000	20	21	1-102203-8
				₇	2.120	2.040	1.900	19	20	1-102203-7
		₁₀	OBSOLETE	₇	2.020	1.940	1.800	18	19	1-102203-6
				₇	1.920	1.840	1.700	17	18	1-102203-5
		₁₀	OBSOLETE	₇	1.820	1.740	1.600	16	17	1-102203-4
				₇	1.720	1.640	1.500	15	16	1-102203-3
				₇	1.620	1.540	1.400	14	15	1-102203-2
				₇	1.520	1.440	1.300	13	14	1-102203-1
				₇	1.420	1.340	1.200	12	13	1-102203-0
				₇	1.320	1.240	1.100	11	12	102203-9
				₇	1.220	1.140	1.000	10	11	102203-8
				₇	1.120	1.040	.900	9	10	102203-7
		₁₀		₇	1.020	.940	.800	8	9	102203-6
				₇	.920	.840	.700	7	8	102203-5
				₇	.820	.740	.600	6	7	102203-4
				₇	.720	.640	.500	5	6	102203-3
				₇	.620	.540	.400	4	5	102203-2
				₇	.520	.440	.300	3	4	102203-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.RINGLY 11JUN85		 TE Connectivity Ltd.	
		CHK D.DUPLER 11JUN85			
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, MOD II,HEADER,SINGLE ROW .100 C/L, RIGHT ANGLE,WITH .025 SQ POST —	
		APVD —			
		PRODUCT SPEC —			
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		APPLICATION SPEC —		SIZE A2	
		MATERIAL —		FINISH SEE TABLE	
		WEIGHT —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-102203	
				RESTRICTED TO —	
				SCALE 1:1	
				SHEET 2 OF 2	
				REV W1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-102203-1](#)