



P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	REV PERECO-10-000443	25NOV09	KK	AEG
	D	REVISED PER ECO-18-000976	13APR2018	RS	JO



- 1 CAVITY LOCATION DIMENSIONS INCREASE IN INCREMENTS OF 2.54[.100] TOLERANCE NON-CUMULATIVE.
- 2 TRADEMARK MOLDED IN RECESSED AREA
- 3 CUSTOMER PART NUMBER, AMP PART NO., AND DATE CODE MARKED IN AREA SHOWN, WHEN HOUSING SIZE PERMITS (7 POSN OR LARGER). IF SIZE DOES NOT PERMIT, DATE CODE ONLY – MAY BE ROTATED 90 DEG TO FIT.
- 4 CAVITY IDENT MARKED 1.17 ± 0.38 [$.046 \pm .015$]
HIGH CHARACTERS FIRST CAVITY (ONE SIDE)
(FOR PART NO. 102267-1 ONLY)
- 5 CAVITY IDENT MARKED SECOND, EVERY FIFTH AND NEXT TO LAST CAVITY (ONE SIDE) (EXCEPT PART NO. 102267-1)
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	713W30431	10.16 [.400]	2.54 [.100]	5.08 [.200]	4	102267-9
	—	—	—	—	—	—
	—	—	—	—	—	—
	—	—	—	—	—	—
	—	—	—	—	—	—
	—	—	—	—	—	—
OBSOLETE	713W31031	25.40 [1.000]	10.16 [.400]	12.70 [.500]	10	102267-3
	713W30531	12.70 [.500]	5.08 [.200]	5.08 [.200]	5	102267-2
	713W30331	7.62 [.300]	2.54 [.100]	2.54 [.100]	3	102267-1
	CUSTOMER PART NO.	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.BRANDBERG 28JUN94		 TE Connectivity Ltd.	
		CHK P. SREMCICH 28JUN94			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONN. HOUSING, CRIMP SNAP – IN, MOD IV, SINGLE ROW, 2.54[.100] CL, W/ POLARIZATION, DETENT AND MARKING	
		APVD P. SREMCICH 28JUN94			
0 PLC ± – 1 PLC ± – 2 PLC ± .02 3 PLC ± .005 4 PLC ± – ANGLES ± 0° 30°		PRODUCT SPEC — APPLICATION SPEC —			
MATERIAL FLAME RETARDANT THERMOPLASTIC COLOR – BLACK		FINISH — WEIGHT —			
CUSTOMER DRAWING				SIZE A2	CAGE CODE 00779
				DRAWING NO C-102267	RESTRICTED TO —
				SCALE 4:1	SHEET 1 of 1
				REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[102267-2](#)