







- ① COORDINATE DIMENSION APPLIES FROM BASIC LOCATION.
- ② 10 AND 14 POSITION SIZES CONTAIN ONLY ONE SLOT FOR SNAP-IN POLARIZER (MILITARY POLARIZATION) LOCATED AS SHOWN.
- ③ 10 POSITION SIZES CONTAIN ONLY ONE SLOT FOR DUAL POLARIZATION, LOCATED AS SHOWN.
4. RECOMMENDED PRINTED CIRCUIT BOARD THICKNESS IS 3.18 [.125].
- ⑤ DISTANCE REQUIRED BY EJECTION LATCHES IN THE OPEN POSITION.
- ⑥ POSTS: GOLD FLASH OVER PALLADIUM-NICKEL PLATE,
0.76 μ m[.000030] MIN TOTAL ON THE LOCALIZED PLATE AREA,
2.54 μ m[.000100] MIN TIN-LEAD PLATE ON THE SOLDER-TAIL,
1.27 μ m[.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.
-OR-
0.76 μ m[.000030] MIN GOLD PLATE ON THE LOCALIZED PLATE AREA,
2.54 μ m[.000100] MIN TIN-LEAD PLATE ON THE SOLDER-TAIL,
1.27 μ m[.000050] MIN NICKEL UNDERPLATE ON THE ENTIRE POST.



H	OBSOLETE	53.34	71.12	65.02	75.18	71.12	60.96	44	1-102321-3
		[2.100]	[2.800]	[2.560]	[2.960]	[2.800]	[2.400]		
		78.74	96.52	90.42	100.58	96.52	86.36	64	1-102321-2
		[3.100]	[3.800]	[3.560]	[3.960]	[3.800]	[3.400]		
		73.66	91.44	85.34	95.50	91.44	81.28	60	1-102321-1
		[2.900]	[3.600]	[3.360]	[3.760]	[3.600]	[3.200]		
		60.96	78.74	72.64	82.80	78.74	68.58	50	1-102321-0
		[2.400]	[3.100]	[2.860]	[3.260]	[3.100]	[2.700]		
		48.26	66.04	59.94	70.10	66.04	55.88	40	102321-9
		[1.900]	[2.600]	[2.360]	[2.760]	[2.600]	[2.200]		
		40.64	58.42	52.32	62.48	58.42	48.26	34	102321-8
		[1.600]	[2.300]	[2.060]	[2.460]	[2.300]	[1.900]		
		35.56	53.34	47.24	57.40	53.34	43.18	30	102321-7
		[1.400]	[2.100]	[1.860]	[2.260]	[2.100]	[1.700]		
		30.48	48.26	42.16	52.32	48.26	38.10	26	102321-6
	I	OBSOLETE	[1.200]	[1.900]	[1.660]	[2.060]	[1.900]	[1.500]	
27.94			45.72	39.62	49.78	45.72	35.56	24	102321-5
[1.100]			[1.800]	[1.560]	[1.960]	[1.800]	[1.400]		
		22.86	40.64	34.54	44.70	40.64	30.48	20	102321-4
		[.900]	[1.600]	[1.360]	[1.760]	[1.600]	[1.200]		
		17.78	35.56	29.46	39.62	35.56	25.40	16	102321-3
		[.700]	[1.400]	[1.160]	[1.560]	[1.400]	[1.000]		
		15.24	33.02	26.92	37.08	33.02	22.86	14	102321-2
		[.600]	[1.300]	[1.060]	[1.460]	[1.300]	[.900]		
		10.16	27.94	21.84	32.00	27.94	17.78	10	102321-1
		[.400]	[1.100]	[.860]	[1.260]	[1.100]	[.700]		
		F	E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN H.MOLL 4-23-90 CHK STONE 11-28-90 R 11-29-90		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		NAME #PVD S. GOOD PRODUCT SPEC 108-40018 APPLICATION SPEC - SIZE A1	
MATERIAL HOUSING & LATCHES: GLASS FILLED NYLON OR POLYESTER, WAFER MOUNT, BLACK POSTS: PHOS BRONZE OR BRASS 		WEIGHT - CUSTOMER DRAWING		DRAWING NO 102321 RESTRICTED TO - SCALE 4:1 SHEET 1 of 1 REV K	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[102321-1](#)