



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	-
© COPYRIGHT 1997	ALL RIGHTS RESERVED.	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		G11	ECR-16-016696	11SEP2017	GR	MKO
			G12	ECR-16-016780	15NOV2017	GR	MKO
			G13	ECR-17-014011	27MAR2018	SG	MKO
			G14	ECR-18-009334	21DEC2018	SR	MKO

NOTES

- 1 PARTS SHALL BE FREE AND CLEAN OF SHARP EDGES AND ALL OTHER FOREIGN MATERIAL NO LOOSE BURRS PERMITTED.
- 2 NBR, 70°±5° SHORE A, BLACK, ACC .TO DIN 3770
- 3 FKM, 70°±5° SHORE A, TEMPERATURE RANGE -30 °C / +200 °C
- 4 EPDM, 65°±5° SHORE A, BLACK, ELECTRICAL CONDUCTIVE, RESISTIVITY: 8.05×10^3 OHMS PER CM
- 5 PACKAGING PN 0-1, 1000 PIECES MAX. IN A BOX


$$A - A$$


SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26.05.1999 Rösger CHK 26.05.1999 Schweiger		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD - PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		NAME 0-Ring - -	
				SIZE A2		CAGE CODE 00779	
MATERIAL -		FINISH -		DRAWING NO C=1106053		RESTRICTED TO	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1	
				REV G14			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1106053-1](#)