






REVISIONS						
P	LTR	DESCRIPTION			DATE	DWN APVD
	L3	PART STATUS	UPDTE IN	PART LIST TABLE	09FEB2018	SD PS

- 1
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 2
- POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3
- FINISH: POSTS:.000015 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 4
- FINISH: POSTS:.000015 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL
- 5
- MATERIALS: HOUSING- FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK
POSTS- PHOS BRONZE
- 6
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMENDED HOLE LAYOUT

OBSOLETE	3.506	.106	3.732	3.600	36	74	8-102618-5
	3.406	.106	3.632	3.500	35	72	8-102618-4
	3.306	.106	3.532	3.400	34	70	8-102618-3
	3.206	.106	3.432	3.300	33	68	8-102618-2
	3.106	.106	3.332	3.200	32	66	8-102618-1
	3.006	.106	3.232	3.100	31	64	8-102618-0
OBSOLETE	2.906	.106	3.132	3.000	30	62	7-102618-9
	2.806	.106	3.032	2.900	29	60	7-102618-8
	2.706	.106	2.932	2.800	28	58	7-102618-7
	2.606	.106	2.832	2.700	27	56	7-102618-6
	2.506	.106	2.732	2.600	26	54	7-102618-5
	2.406	.106	2.632	2.500	25	52	7-102618-4
OBSOLETE	2.306	.106	2.532	2.400	24	50	7-102618-3
	2.206	.106	2.432	2.300	23	48	7-102618-2
	2.106	.106	2.332	2.200	22	46	7-102618-1
	2.006	.106	2.232	2.100	21	44	7-102618-0
	1.906	.106	2.132	2.000	20	42	6-102618-9
	1.806	.106	2.032	1.900	19	40	6-102618-8
OBSOLETE	1.706	.106	1.932	1.800	18	38	6-102618-7
	1.606	.106	1.832	1.700	17	36	6-102618-6
	1.506	.106	1.732	1.600	16	34	6-102618-5
	1.406	.106	1.632	1.500	15	32	6-102618-4
	1.306	.106	1.532	1.400	14	30	6-102618-3
	1.206	.106	1.432	1.300	13	28	6-102618-2
OBSOLETE	1.106	.106	1.332	1.200	12	26	6-102618-1
	1.006	.106	1.232	1.100	11	24	6-102618-0
	.906	.106	1.132	1.000	10	22	5-102618-9
	.806	.106	1.032	.900	9	20	5-102618-8
	—	.406	.932	.800	8	18	5-102618-7
	—	.306	.832	.700	7	16	5-102618-6
OBSOLETE	—	.306	.732	.600	6	14	5-102618-5
	—	.206	.632	.500	5	12	5-102618-4
	—	.206	.532	.400	4	10	5-102618-3
	—	.106	.432	.300	3	8	5-102618-2
	—	.106	.332	.200	2	6	5-102618-1
OBSOLETE	3.506	.106	3.732	3.600	36	74	3-102618-5
	3.406	.106	3.632	3.500	35	72	3-102618-4
	3.306	.106	3.532	3.400	34	70	3-102618-3
	3.206	.106	3.432	3.300	33	68	3-102618-2
	3.106	.106	3.332	3.200	32	66	3-102618-1
	3.006	.106	3.232	3.100	31	64	3-102618-0
OBSOLETE	2.906	.106	3.132	3.000	30	62	2-102618-9
	2.806	.106	3.032	2.900	29	60	2-102618-8
	2.706	.106	2.932	2.800	28	58	2-102618-7
	2.606	.106	2.832	2.700	27	56	2-102618-6
	2.506	.106	2.732	2.600	26	54	2-102618-5
	2.406	.106	2.632	2.500	25	52	2-102618-4
OBSOLETE	2.306	.106	2.532	2.400	24	50	2-102618-3
	2.206	.106	2.432	2.300	23	48	2-102618-2
	2.106	.106	2.332	2.200	22	46	2-102618-1
	2.006	.106	2.232	2.100	21	44	2-102618-0
	1.906	.106	2.132	2.000	20	42	1-102618-9
	1.806	.106	2.032	1.900	19	40	1-102618-8
OBSOLETE	1.706	.106	1.932	1.800	18	38	1-102618-7
	1.606	.106	1.832	1.700	17	36	1-102618-6
	1.506	.106	1.732	1.600	16	34	1-102618-5
	1.406	.106	1.632	1.500	15	32	1-102618-4
	1.306	.106	1.532	1.400	14	30	1-102618-3
	1.206	.106	1.432	1.300	13	28	1-102618-2
OBSOLETE	1.106	.106	1.332	1.200	12	26	1-102618-1
	1.006	.106	1.232	1.100	11	24	1-102618-0
	.906	.106	1.132	1.000	10	22	—102618-9
	.806	.106	1.032	.900	9	20	102618-8
	—	.406	.932	.800	8	18	102618-7
	—	.306	.832	.700	7	16	102618-6
OBSOLETE	—	.306	.732	.600	6	14	102618-5
	—	.206	.632	.500	5	12	102618-4
	—	.206	.532	.400	4	10	102618-3
	—	.106	.432	.300	3	8	102618-2
	—	.106	.332	.200	2	6	102618-1
	—	.106	.332	.200	2	6	102618-1
PLATING	E	D	C	B	A	NO. OF POSN	ASSEMBLY PART NUMBER

SUP BY 5-102618-9

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

APPROVED: R. FEIDT

DATE: 4-9-87

NAME:

SIZE: A1

CAGE CODE: 00779

DRAWING NO: 102618

WEIGHT: —

CUSTOMER DRAWING

DWN: H. MOLL

CHK: LA. MAYER

APPROVED: R. FEIDT

DATE: 4-9-87

NAME:

TE Connectivity

ASSEMBLY, HEADER, MOD II, .025 SQ POST, DBL ROW, .100 X .100 C/L WITH DETENTS

SCALE: 4:1

SHEET 1 OF 1

REV L3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-102618-5](#)