







PN 0-1, 0-3 & 0-5



PN 0-2,0-4 & 0-7




PN 0-6 & 0-8



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A8	REVISED PER ECR-16-016780	19SEP2017	NG	MKO

NOTES

- 1 Material: Housing: Aluminum diecasting alloy
seals: Neoprene
- 2 Surface:- Aluminium oxide + Varnish Black
-Grey
- 3 Varnish on the inside not necessary
- ⚠ Special- Logo
- 5 Packaging quantity 5 pieces in a box



OBSOLETE																
1									Hood HIP-K	Aluminium	Aluminium oxide	Blackl	8	Without Logo/thread		
	1								Hood HIP	Aluminium		Without varnish	7			
		1							Hood HIP-K	Aluminium	Aluminium oxide	Without varnish	6	Without M-Thread		
2	2	2	2	2	2	2	2		Pane	Stainless steel	Blank		5	B6.4		
2	2	2	2	2	2	2	2		Fixing screw	Stainless steel	Blank		4	M6x30		
1	1	1	1	1	1	1	1		Seal	Neoprene		Black	3			
					1	1			Hood HIP-K	Aluminium	Aluminium oxide	Black	2			
						1			Hood HIP	Aluminium		Grey	1			
0-8	0	7	0	6	0	5	0-4	0-2	0-3	0-1	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM NO	REMARKS
ORDERING TEXT																
⚠ HIP.24/64.ST0.1.M40.G																
HIP.24/64.ST0.1.M40.G																
HIP.24/64.STS.1.M40.G																
HIP-K.24/64.STS.1.M40.G																
HIP-K.24/64.STS.1.M32.G																
HIP-K.24/64.ST																
HIP.24/64.STS.1.M40.G																

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN Schneider 10.09.02		TE Connectivity	
				CHK Schweizer 10.09.02			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME	
mm		0 PLC ±		108-74030		Hood	
		2 PLC ±		APPLICATION SPEC		HIP.24/64.1.M32/M40.G	
		3 PLC ±		116-74017		SIZE CAGE CODE DRAWING NO	
		4 PLC ±		WEIGHT		A 1 00779 C=1106473	
		ANGLES FINISH		CUSTOMER DRAW ING		RESTRICTED TO	
				SCALE 1:1		SHEET 1 OF 1	
						REV A8	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1106473-8](#)