





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E4	NEW PART NO 1394759-6 ADDED	06DEC2017	SV	PKS
	E5	1394759-6 RELEASE FOR PRODUCTION	30MAY2018	SV	PKS
	F	REVISED PER ECR-19-009725	02JUL2019	BDA	SV
	F1	REVISED PER ECR-19-015041	06NOV2019	PC	MB



- 1 SLOT ACCEPTS:
SINGLE OR DOUBLE MAGNET WIRE
0.63...0.85 mm DIA
Kontakt geeignet fuer :
Lackdraht, Einzeldraht und Doppeldraht
Ø0.63...0.85 mm
- 2 POKE IN TAB TERMINAL 3.4x0.5mm
Poke in Flachstecker 3.4x0.5mm
- 3 AREA WILL BE CUT BY TERMINATION
Bereich wird beim Kontaktieren abgetrennt
- 4 CAVITY ACCORDING TO TE SPEC. 411-18512
Kontakt Kammer nach TE Spec. 411-18512
- 5 IDENTIFICATION NO. FOR MAGNET WIRE RANGE (20)
Kennziffer fuer Lackdrahtbereich (20)
- 6 REELED WITH INTERLEAVE PAPER.
ABGEWICKELT MIT INTERLEAVE-PAPIER.

1394759-6	-	CuNiSi	NICKEL PLATED	MAG MATE LEAF TERMINAL	-
1394759-5	-	CuNiSi	TIN PLATED	MAG MATE LEAF TERMINAL	-
1394759-3	-	CuZn	PRE TINNED	MAG MATE LEAF TERMINAL	-
1394759-2	-	CuNiSi	PRE TINNED	MAG MATE LEAF TERMINAL	-
1394759-1	-	CuNiSi	BLANK	MAG MATE LEAF TERMINAL	-
PART NO	PCS.	MATERIAL	SURFACE COLOUR	DESCRIPTION	ITEM NO



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. ATZMANN 04-01-01	 TE Connectivity					
		CHK H. Plöber 04-01-01						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: n. ISO 8015, n. ISO 2768- mm-E n. DIN 16001-140	APVD -	NAME MAG MATE LEAF TERMINAL MARK II				
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°	PRODUCT SPEC 108-2012					
MATERIAL SEE TABLE		FINISH SEE TABLE	APPLICATION SPEC 114-2046	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
			WEIGHT -	A 3	00779	C-1394759		-
CUSTOMER DRAWING						SCALE 10:1	SHEET 1 OF 1	REV F1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1394759-1](#)