

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.



© COPYRIGHT

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	K4	New 24 pos part number 6-102699-1 added	01AUG2016	KJK	PS



SECTION X-X




RECOMMENDED HOLE LAYOUT

NOTES:

- 1 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 MATERIAL: HOUSING- FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK
POSTS- COPPER ALLOY
- 4 FINISH: POSTS- .000030 GOLD ON CONTACT AREA,
.000100-.000200 MATTE TIN-LEAD ON SOLDERTAIL,
ALL OVER .000050 NICKEL
- 5 FINISH: POSTS- .000030 GOLD ON CONTACT AREA,
.000100-.000200 MATTE TIN ON SOLDERTAIL,
ALL OVER .000050 NICKEL
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	OBSOLETE	2.806	.106	3.032	2.900	29	60	7-102699-8
		2.306	.106	2.532	2.400	24	50	7-102699-3
		1.806	.106	2.032	1.900	19	40	6-102699-9
		1.506	.106	1.732	1.600	16	34	6-102699-6
		1.306	.106	1.532	1.400	14	30	6-102699-4
		1.106	.106	1.332	1.200	12	26	6-102699-2
		1.006	.106	1.232	1.100	10	24	6-102699-1
		.806	.106	1.032	.900	9	20	5-102699-9
		—	.406	.932	.800	8	18	5-102699-8
		—	.306	.832	.700	7	16	5-102699-7
		—	.306	.732	.600	6	14	5-102699-6
		—	.206	.632	.500	5	12	5-102699-5
		—	.206	.532	.400	4	10	5-102699-4
		—	.106	.432	.300	3	8	5-102699-3
		—	.106	.332	.200	2	6	5-102699-2
	6	OBSOLETE	2.806	.106	3.032	2.900	29	60
OBSOLETE		2.706	.106	2.932	2.800	28	58	2-102699-7
OBSOLETE		2.606	.106	2.832	2.700	27	56	2-102699-6
OBSOLETE		2.506	.106	2.732	2.600	26	54	2-102699-5
OBSOLETE		2.406	.106	2.632	2.500	25	52	2-102699-4
		2.306	.106	2.532	2.400	24	50	2-102699-3
OBSOLETE		2.206	.106	2.432	2.300	23	48	2-102699-2
OBSOLETE		2.106	.106	2.332	2.200	22	46	2-102699-1
OBSOLETE		1.906	.106	2.132	2.000	20	42	2-102699-0
		1.806	.106	2.032	1.900	19	40	1-102699-9
6	SUP BY 6-102699-6	1.706	.106	1.932	1.800	18	38	1-102699-8
		1.606	.106	1.832	1.700	17	36	1-102699-7
		1.506	.106	1.732	1.600	16	34	1-102699-6
		1.406	.106	1.632	1.500	15	32	1-102699-5
		1.306	.106	1.532	1.400	14	30	1-102699-4
	OBSOLETE	1.206	.106	1.432	1.300	13	28	1-102699-3
		1.106	.106	1.332	1.200	12	26	1-102699-2
	OBSOLETE	1.006	.106	1.232	1.100	11	24	1-102699-1
	OBSOLETE	.906	.106	1.132	1.000	10	22	1-102699-0
		.806	.106	1.032	.900	9	20	102699-9
		—	.406	.932	.800	8	18	102699-8
		—	.306	.832	.700	7	16	102699-7
		—	.306	.732	.600	6	14	102699-6
		—	.206	.632	.500	5	12	102699-5
		—	.206	.532	.400	4	10	102699-4
		—	.106	.432	.300	3	8	102699-3
	—	.106	.332	.200	2	6	102699-2	
	OBSOLETE	2.006	.106	2.232	2.100	21	44	102699-1
	FINISH	E	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN R BROWN 14APROS		 TE Connectivity			
				CHK R BROWN 14APROS					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D J GEFORD 14APROS		NAME HDR ASSY, MOD II, COMPLIANT PIN, DBL ROW, .100x.100 CL, SIDE SHROUD			
				PRODUCT SPEC —					
		APPLICATION SPEC —		SIZE		CAGE CODE		DRAWING NO	
				WEIGHT		A1		00779	
MATERIAL —		FINISH SEE TABLE						RESTRICTED TO —	
CUSTOMER DRAWING									
				SCALE		4:1		SHEET 1 of 1	
				REV		K4			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[102699-9](#)