





LOC		DIST		REVISIONS				
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		D6		REV PER ECR-12-018227	24OCT2012	CZ	SZ	
		D8		ADDED NEW DASH NUMBER 1-2	30MAY2016	CZ	SZ	
		D9		ADDED NEW DASH NUMBER 1-3	12AUG2016	CZ	SZ	



SCALE 2:1




- 1 DIM S IS CENTERLINE SPACING OF POWER MODULES.
- 2 COMPANY TRADEMARK, PART NUMBER, AND DATE CODE TO BE MARKED IN AREA SHOWN PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
3. MATERIAL: THERMO PLASTIC, UL94 V-0.BLACK.
- 4 DATUM LOCATIONS AND BASIC DIMENSIONS TO BE ESTABLISHED BY THE CUSTOMER.
- 5 BULKHEAD THICKNESS RANGE: .031 - .100.
- 6 CONNECTOR MATED TO PANEL FROM OPPOSITE SIDE.
- 7 NO BURRS ALLOWED ON OPPOSITE (MATING) SIDE.
- 8 CONNECTOR KEEP OUT ZONE.
- 9 MOUNT CONNECTOR WITH TYCO HARDWARE KIT P/N 1600914-1 FOR .050 (1.27mm) MIN RADIAL FLOAT.
- 10 LOCATION OF GROUND SYMBOL ON MFBL CAVITY, FOR 1600606-2 ONLY.
- 11 THE SPECIAL BULKHEAD LAYOUT IS ONLY FOR PN:1600606-2 WITH RESTRICT FLOATING.

D9	1.200	.300	1.550	.475	2.110	2.600	3ACP	1-1600606-3
	.800	.250	1.150	.450	1.710	2.200	2P	1-1600606-2
	1.800	.300	2.150	.475	2.710	3.200	5ACP	1-1600606-1
	2.050	.250	2.400	.450	2.960	3.450	7P	1-1600606-0
	1.725	.375	2.075	.475	2.635	3.125	4P	1600606-9
	2.050	.300	2.400	.450	2.960	3.450	6ACP	1600606-8
	2.100	.300	2.450	.475	3.010	3.500	6ACP	1600606-7
	2.825	.425	3.175	.525	3.735	4.225	6ACP	1600606-6
	2.500	.300	2.850	.525	3.410	3.900	7ACP	1600606-5
	1.900	.300	2.250	.525	2.810	3.300	5ACP	1600606-4
	3.000	.300	3.350	.475	3.910	4.400	9ACP	1600606-3
	1.200	.300	1.550	.475	2.110	2.600	3ACP	1600606-2
	1.550	.250	1.900	.450	2.460	2.950	5P	1600606-1
	DIM U	DIM S	DIM L	DIM K	DIM E	DIM F	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.GRZYBOWSKI 23JUL2003	CHG M.CORRELL 23JUL2003		APVD -		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-2157		NAME PANEL MOUNT CABLE RECEPTACLE HOUSING, WITH GUIDES, MULTI-BEAM XL, ALL POWER		
		0 PLC ±.01 1 PLC ±.01 2 PLC ±.005 4 PLC ±.0020 ANGLES ±.75°		APPLICATION SPEC 114-13112		SIZE A100779C=1600606		
MATERIAL -		FINISH -		WEIGHT -		RESTRICTED TO -		
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 3		
						REV D9		

PART NUMBER		POWER						
		P6	P5	P4	P3	P2	P1	
1600606-6								
6ACP								

[illegible][illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 23JUL2003 CHG. 23JUL2003 M. GRZYBOWSKI M. CORRELL APVD.		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: DECIMALS: .010 FRACTIONS: 1/32 ANGLES: ±0°		NAME: PANEL MOUNT CABLE RECEPTACLE HOUSING, WITH GUIDES, MULTI-BEAM XL, ALL POWER	
MATERIAL: - FINISH: -		PRODUCT SPEC: 108-2157 APPLICATION SPEC: 114-13112 WEIGHT: -		SIZE: CAGE CODE: DRAWING NO: A100779C SCALE: 4:1 SHEET: 2 of 3 REV'D: 0	
CUSTOMER DRAWING		RESTRICTED TO			

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	SEE SHEET 1	-	-	-	

D

PART NUMBER		POWER						
		P6	P5	P4	P3	P2	P1	
1600606-7		RM	RM	RM	RM	RM	RM	
6ACP								

PART NUMBER		POWER						
		P6	P5	P4	P3	P2	P1	
1600606-8		RM	RM	RM	RM	RM	RM	
6ACP								

PART NUMBER		POWER				
		P4	P3	P2	P1	
1600606-9		RA	RM	RM	RM	
4P						

PART NUMBER		POWER							
		P7	P6	P5	P4	P3	P2	P1	
1-1600606-0		RM		RM		RM		RA	
7P									

PART NUMBER		POWER					
		P5	P4	P3	P2	P1	
1-1600606-1		RM	RM	RM	RM	RM	
5ACP							

PART NUMBER		POWER		
		P2	P1	
1-1600606-2		RM	RA	
2P				

PART NUMBER		POWER			
		P3	P2	P1	
1-1600606-3		RA	RM	RM	
3ACP					

D9

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.GRZYBOWSKI 23JUL2003	 TE Connectivity	
		CHK M.CORRELL 23JUL2003		
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±" 1 PLC ±.01 2 PLC ±.01 3 PLC ±.005 4 PLC ±.0020 ANGLES ±2° FINISH	PRODUCT SPEC 108-2157 APPLICATION SPEC 114-13112	
MATERIAL -		WEIGHT -	SIZE A1	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C=1600606	RESTRICTED TO -
		SCALE 4:1	SHEET 3	OF 3
		REV D9		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1600606-2](#)