

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		G	REVISED PER ECO-14-000068	23APR2014	NK	MM

- 1



ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2

THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 3

POINT OF MEASUREMENT FOR PLATING THICKNESS
- 4

BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 5

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



	OBSOLETE	3.984	3.900	39	40	4-103148-0		
		3.884	3.800	38	39	3-103148-9		
		3.784	3.700	37	38	3-103148-8		
		3.684	3.600	36	37	3-103148-7		
SUPERSEDED BY 8-146304-6		3.584	3.500	35	36	3-103148-6		
	OBSOLETE	3.484	3.400	34	35	3-103148-5		
		3.384	3.300	33	34	3-103148-4		
		3.284	3.200	32	33	3-103148-3		
		3.184	3.100	31	32	3-103148-2		
		3.084	3.000	30	31	3-103148-1		
		2.984	2.900	29	30	3-103148-0		
		2.884	2.800	28	29	2-103148-9		
		2.784	2.700	27	28	2-103148-8		
		2.684	2.600	26	27	2-103148-7		
SUPERSEDED BY 7-146304-5		2.584	2.500	25	26	2-103148-6		
	OBSOLETE	2.484	2.400	24	25	2-103148-5		
		2.384	2.300	23	24	2-103148-4		
		2.284	2.200	22	23	2-103148-3		
		2.184	2.100	21	22	2-103148-2		
		2.084	2.000	20	21	2-103148-1		
		1.984	1.900	19	20	2-103148-0		
		1.884	1.800	18	19	1-103148-9		
		1.784	1.700	17	18	1-103148-8		
	OBSOLETE	1.684	1.600	16	17	1-103148-7		
		1.584	1.500	15	16	1-103148-6		
		1.484	1.400	14	15	1-103148-5		
		1.384	1.300	13	14	1-103148-4		
		1.284	1.200	12	13	1-103148-3		
		1.184	1.100	11	12	1-103148-2		
		SUPERSEDED BY 6-146304-2		1.084	1.000	10	11	1-103148-1
			OBSOLETE	.984	.900	9	10	1-103148-0
.884	.800			8	9	103148-9		
.784	.700			7	8	103148-8		
.684	.600			6	7	103148-7		
.584	.500			5	6	103148-6		
.484	.400			4	5	103148-5		
SUPERSEDED BY 5-146304-9				.384	.300	3	4	103148-4
	OBSOLETE			.284	.200	2	3	103148-3
		.184	.100	1	2	103148-2		
		SUPERSEDED BY 4-146304-8		.084	—	—	1	103148-1
		C	B	A	NO OF POSN	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 23OCT87		 TE Connectivity					
DIMENSIONS: INCHES		CHK T. CLARK 23OCT87							
		APVD T. CLARK 29OCT87		NAME HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100CL, RIGHT ANGLE, WITH .025 SQ POSTS					
		PRODUCT SPEC —							
		APPLICATION SPEC —							
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK POSTS: COPPER ALLOY		FINISH : POSTS .000030 GOLD ON CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT —		A2 00779		C=103148			
CUSTOMER DRAWING				SCALE	4:1	SHEET	1 of 1	REV	G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103148-3](#)