

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 2020 TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	9	INITIAL CUSTOMER DRAWING	10FEB2020	AFK	LS

NOTES:-

1. CHARACTERS:-
0-9, A-Z, +, -, /, ~ & ±
0, 1, 6 & 9 ARE FOLLOWED BY A FULL STOP
TOLERANCE (AXIAL) ±0.75
(ROTATIONAL) ±5°

The drawing shows two views of a marker. The left view is an end view showing an elliptical shape with dimensions: 'A' for height, 'B' for width, and 'T' for thickness. The right view is a side view showing a rectangular shape with dimensions: 'L' for length and 'C' for height. The height 'C' is also labeled as 'nom.' (nominal). A dashed centerline is shown in both views.

DESCRIPTION (1st 4 DIGITS)	SIZE	"A"	"B"	CHARACTER HEIGHT "C"	"L"	"T"	WEIGHT / 250mm
1358	30	4.95 – 5.25	1.30 – 1.60	2.4	4.25 – 4.75	0.68 – 0.78	2.94 – 3.24
1361	65	9.90 – 10.2	2.90 – 3.20	4.0	5.50 – 6.00	1.18 – 1.28	9.57 – 10.57

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
PVC

FINISH
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

DWN
AFK

CHK
-

APVD
-

PRODUCT SPEC
RW-2535

APPLICATION SPEC
-

WEIGHT
SEE TABLE

CUSTOMER DRAWING

07FEB2020

TE Connectivity

NAME
MARKER, K TYPE

SIZE
A3

CAGE CODE
0198G

DRAWING NO
C-1602A0001

RESTRICTED TO
-

SCALE
-

SHEET
1 OF 1

REV
9

1470-19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EC6533-000](#)