

DO NOT SCALE  
DIMENSIONS IN mm

METRIC






ROUND ANGLE  
PROJECTION



NOTES:

1 FOR USE ON MINIATURE APPLICATORS ( LEFT-RIGHT FEED )  
AND STANDARD APPLICATORS ( RIGHT-LEFT FEED ).

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION A-A

SECTION B-B

WIRE RANGE :  
0.5-1.0 mm<sup>2</sup>  
INSULATION RANGE :  
2.0-3.0mm DIA.

DIRECTION OFF TOP OF REEL



Terminal "U" up.

2 OBSOLETE

PRE-TINPLATED	PH. BRONZE	160626-9
SILVERPLATED	BRASS	160626-3
TINPLATED	BRASS	160626-2
UNPLATED	BRASS	160626-1
NOTES	FINISH	MATERIAL
PARTNUMBER		

CUSTOMER DRAWING				FOR REFERENCE ONLY WILL NOT BE UPDATED	
© COPYRIGHT IS - BY AMP HOLLAND B.V.				ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.	
THIS DRAWING IS UNPUBLISHED				RELEASED FOR PUBLICATION	
AMP				AMP HOLLAND B.V. s-Hertogenbosch, The Netherlands.	
NAME				.110 SRS FASTON RECEPTACLE.LP	
A1	REVISED PER ECO-09-022178	KK	AEG	25/09/09	
A	H-9701	Just	AS	08-04-82	
REVISION RECORD		DR.	CHK.	DATE	
DR. J.T.S. REUSE	CHK. J. A. B. A. B.	APP. J. L. B. E. R.	DATE: 08-04-82		
DATE: 08-04-82	DATE: -	DATE: 24-4-92	C-160626		
SHEET				1 OF 3	REV. I.T.R. A1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[160626-2](#)