


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H1	REVISED PER ECO-16-012733	07SEP2016	NK	MM

- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



OBSOLETE 5	3.984	3.900	39	80	4-103240-0
	3.884	3.800	38	78	3-103240-9
	3.784	3.700	37	76	3-103240-8
	3.684	3.600	36	74	3-103240-7
	3.584	3.500	35	72	3-103240-6
OBSOLETE 5	3.484	3.400	34	70	3-103240-5
	3.384	3.300	33	68	3-103240-4
	3.284	3.200	32	66	3-103240-3
	3.184	3.100	31	64	3-103240-2
	3.084	3.000	30	62	3-103240-1
5 OBSOLETE	2.984	2.900	29	60	3-103240-0
	2.884	2.800	28	58	2-103240-9
	2.784	2.700	27	56	2-103240-8
5 OBSOLETE	2.684	2.600	26	54	2-103240-7
	2.584	2.500	25	52	2-103240-6
	2.484	2.400	24	50	2-103240-5
5 OBSOLETE	2.384	2.300	23	48	2-103240-4
	2.284	2.200	22	46	2-103240-3
	2.184	2.100	21	44	2-103240-2
5 OBSOLETE	2.084	2.000	20	42	2-103240-1
	1.984	1.900	19	40	2-103240-0
	1.884	1.800	18	38	1-103240-9
5 OBSOLETE	1.784	1.700	17	36	1-103240-8
	1.684	1.600	16	34	1-103240-7
	1.584	1.500	15	32	1-103240-6
5 SUPERSEDED BY 6-146257-1	1.484	1.400	14	30	1-103240-5
5 SUPERSEDED BY 6-146257-3	1.384	1.300	13	28	1-103240-4
5 SUPERSEDED BY 6-146257-5	1.284	1.200	12	26	1-103240-3
	1.184	1.100	11	24	1-103240-2
	1.084	1.000	10	22	1-103240-1
	.984	.900	9	20	1-103240-0
	.884	.800	8	18	103240-9
	.784	.700	7	16	103240-8
	.684	.600	6	14	103240-7
	.584	.500	5	12	103240-6
	.484	.400	4	10	103240-5
	.384	.300	3	8	103240-4
	.284	.200	2	6	103240-3
	.184	.100	1	4	103240-2
	.084	—	—	2	103240-1
	C	B	A	NO OF POSN	PART NUMBER

RECOMMENDED HOLE LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
H MOLL
CHK
T. CLARK
APVD
T. CLARK
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
—

13OCT87
20OCT87
20OCT87

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

MATERIAL
HOUSING: FLAME RETARDANT
THERMOPLASTIC
COLOR-BLACK
POST: COPPER ALLOY

FINISH : POST:
.000030 GOLD ON CONTACT AREA,
000100-.000200 MATTE
TIN-LEAD ON SOLDER TAIL
ALL OVER .000050 NICKEL

TE Connectivity

NAME
HEADER ASSY, MOD II, BREAKAWAY,
DOUBLE ROW, .100X.100 Q, VERTICAL,
WITH .025 SQ POSTS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=103240

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
H1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103240-6](#)