



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	J1	REVISED PER ECO-21-000268	13JAN2021	RK	JO



RECOMMENDED HOLE LAYOUT

- | | |
|---|--|
| 1 | ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS. |
| 2 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING |
| 3 | POINT OF MEASUREMENT FOR PLATING THICKNESS |
| 4 | SINGLE TUBING PACKAGING |
| 5 | BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT |
| 6 | FINISH: POSTS— .000015 GOLD ON CONTACT AREA, .000100—.000200
MATTE TIN—LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL |
| 7 | FINISH: POSTS— .000015 GOLD ON CONTACT AREA, .000100—.000200
MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL |
| 8 | HIGH TEMPERATURE CONFIGURATION |

$\frac{8}{8}$	$\frac{7}{7}$	$\frac{4}{4}$	.384	.300	3	4	9-103325-1
$\frac{8}{8}$	$\frac{7}{7}$		3.984	3.900	39	40	9-103325-0
$\frac{8}{8}$	$\frac{7}{7}$		3.884	3.800	38	39	8-103325-9
$\frac{8}{8}$	$\frac{7}{7}$		3.784	3.700	37	38	8-103325-8
$\frac{8}{8}$	$\frac{7}{7}$		3.684	3.600	36	37	8-103325-7
$\frac{8}{8}$	$\frac{7}{7}$		3.584	3.500	35	36	8-103325-6
$\frac{8}{8}$	$\frac{7}{7}$		3.484	3.400	34	35	8-103325-5
$\frac{8}{8}$	$\frac{7}{7}$		3.384	3.300	33	34	8-103325-4
$\frac{8}{8}$	$\frac{7}{7}$		3.284	3.200	32	33	8-103325-3
$\frac{8}{8}$	$\frac{7}{7}$		3.184	3.100	31	32	8-103325-2
$\frac{8}{8}$	$\frac{7}{7}$		3.084	3.000	30	31	8-103325-1
$\frac{8}{8}$	$\frac{7}{7}$		2.984	2.900	29	30	8-103325-0
$\frac{8}{8}$	$\frac{7}{7}$		2.884	2.800	28	29	7-103325-9
$\frac{8}{8}$	$\frac{7}{7}$		2.784	2.700	27	28	7-103325-8
$\frac{8}{8}$	$\frac{7}{7}$		2.684	2.600	26	27	7-103325-7
$\frac{8}{8}$	$\frac{7}{7}$		2.584	2.500	25	26	7-103325-6
$\frac{8}{8}$	$\frac{7}{7}$		2.484	2.400	24	25	7-103325-5
$\frac{8}{8}$	$\frac{7}{7}$		2.384	2.300	23	24	7-103325-4
$\frac{8}{8}$	$\frac{7}{7}$		2.284	2.200	22	23	7-103325-3
$\frac{8}{8}$	$\frac{7}{7}$		2.184	2.100	21	22	7-103325-2
$\frac{8}{8}$	$\frac{7}{7}$		2.084	2.000	20	21	7-103325-1
$\frac{8}{8}$	$\frac{7}{7}$		1.984	1.900	19	20	7-103325-0
$\frac{8}{8}$	$\frac{7}{7}$		1.884	1.800	18	19	6-103325-9
$\frac{8}{8}$	$\frac{7}{7}$		1.784	1.700	17	18	6-103325-8
$\frac{8}{8}$	$\frac{7}{7}$		1.684	1.600	16	17	6-103325-7
$\frac{8}{8}$	$\frac{7}{7}$		1.584	1.500	15	16	6-103325-6
$\frac{8}{8}$	$\frac{7}{7}$		1.484	1.400	14	15	6-103325-5
$\frac{8}{8}$	$\frac{7}{7}$		1.384	1.300	13	14	6-103325-4
$\frac{8}{8}$	$\frac{7}{7}$		1.284	1.200	12	13	6-103325-3
$\frac{8}{8}$	$\frac{7}{7}$		1.184	1.100	11	12	6-103325-2
$\frac{8}{8}$	$\frac{7}{7}$		1.084	1.000	10	11	6-103325-1
$\frac{8}{8}$	$\frac{7}{7}$		.984	.900	9	10	6-103325-0
$\frac{8}{8}$	$\frac{7}{7}$		.884	.800	8	9	5-103325-9
$\frac{8}{8}$	$\frac{7}{7}$		.784	.700	7	8	5-103325-8
$\frac{8}{8}$	$\frac{7}{7}$		.684	.600	6	7	5-103325-7
$\frac{8}{8}$	$\frac{7}{7}$		.584	.500	5	6	5-103325-6
$\frac{8}{8}$	$\frac{7}{7}$		.484	.400	4	5	5-103325-5
$\frac{8}{8}$	$\frac{7}{7}$		.384	.300	3	4	5-103325-4
$\frac{8}{8}$	$\frac{7}{7}$		.284	.200	2	3	5-103325-3
$\frac{8}{8}$	$\frac{7}{7}$		.184	.100	1	2	5-103325-2
$\frac{8}{8}$	$\frac{7}{7}$		.084	—	—	1	5-103325-1

	$\triangle_6$	$\triangle_4$	3.84	.300	3	4	4-103325-1
	$\triangle_6$		3.984	3.900	39	40	4-103325-0
	$\triangle_6$		3.884	3.800	38	39	3-103325-9
	$\triangle_6$		3.784	3.700	37	38	3-103325-8
	$\triangle_6$		3.684	3.600	36	37	3-103325-7
	$\triangle_6$		3.584	3.500	35	36	3-103325-6
	$\triangle_6$		3.484	3.400	34	35	3-103325-5
	$\triangle_6$		3.384	3.300	33	34	3-103325-4
	$\triangle_6$		3.284	3.200	32	33	3-103325-3
	$\triangle_6$		3.184	3.100	31	32	3-103325-2
	$\triangle_6$		3.084	3.000	30	31	3-103325-1
	$\triangle_6$		2.984	2.900	29	30	3-103325-0
	$\triangle_6$		2.884	2.800	28	29	2-103325-9
	$\triangle_6$		2.784	2.700	27	28	2-103325-8
	$\triangle_6$		2.684	2.600	26	27	2-103325-7
	$\triangle_6$		2.584	2.500	25	26	2-103325-6
	$\triangle_6$		2.484	2.400	24	25	2-103325-5
	$\triangle_6$		2.384	2.300	23	24	2-103325-4
	$\triangle_6$		2.284	2.200	22	23	2-103325-3
	$\triangle_6$		2.184	2.100	21	22	2-103325-2
	$\triangle_6$		2.084	2.000	20	21	2-103325-1
	$\triangle_6$		1.984	1.900	19	20	2-103325-0
	$\triangle_6$		1.884	1.800	18	19	1-103325-9
	$\triangle_6$		1.784	1.700	17	18	1-103325-8
	$\triangle_6$		1.684	1.600	16	17	1-103325-7
SUPERSEDED	$\triangle_6$		1.584	1.500	15	16	1-103325-6
SUPERSEDED	$\triangle_6$		1.484	1.400	14	15	1-103325-5
	$\triangle_6$		1.384	1.300	13	14	1-103325-4
	$\triangle_6$		1.284	1.200	12	13	1-103325-3
	$\triangle_6$		1.184	1.100	11	12	1-103325-2
	$\triangle_6$		1.084	1.000	10	11	1-103325-1
	$\triangle_6$		.984	.900	9	10	1-103325-0
	$\triangle_6$		.884	.800	8	9	103325-9
	$\triangle_6$		.784	.700	7	8	103325-8
	$\triangle_6$		.684	.600	6	7	103325-7
	$\triangle_6$		.584	.500	5	6	103325-6
SUPERSEDED	$\triangle_6$		.484	.400	4	5	103325-5
	$\triangle_6$		.384	.300	3	4	103325-4
	$\triangle_6$		.284	.200	2	3	103325-3
	$\triangle_6$		.184	.100	1	2	103325-2
	$\triangle_6$		.084	—	—	1	103325-1

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103325-5](#)