

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	REVISED PER ECO-11-005027	12MAR11	RK	HMR
	A5	REVISED PER ECO-17-008114	01JUN2018	RS	DR

D

D

C


C

B

B

A

A



- 1

STAMP "AMP 12-10*", LOCATION APPROX AS SHOWN
- 2

BODY MATERIAL THICKNESS IS 0.991±0.051[.039±.002]
- 3

APPLIES TO EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE
- 4

WIRE INSULATION DIA RANGE 3.810-6.426[.150-.253]
- 5

BODY - COPPER PER ASTM B152
SLEEVE - COPPER PER ASTM B152
INSULATION - NYLON
- 6

BODY - TIN PLATE PER ASTM B545
SLEEVE - TIN PLATE PER ASTM B545
INSULATION - COLOR-YELLOW
- 7

105°C MAX OPERATING TEMP
- 8

300 VOLT MAX
- 9

2.62-6.64mm2 [5,180-13,100 CMA]
SOLID OR STRANDED

500	LOOSE PIECE	165028
QTY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr ruth 29MAR07	TE Connectivity Ltd.			
		CHK T MICHELUTTI 29MAR07				
		APVD T MICHELUTTI 29MAR07	NAME			
DIMENSIONS: mm [INCHES]		PRODUCT SPEC UL 486 A-B	TERMINAL RING TONGUE, PIDG, WIRE SIZE 12-10			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-2157				
MATERIAL		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-165028	RESTRICTED TO -
FINISH		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 1	REV A5	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-165028-1](#)